



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



774016 Toggle Switch, Heavy Duty, DPDT, On-Off-On, Screw

Ideal

Catalog Number	774016
Manufacturer	Ideal
Description	Toggle Switch, 2 Poles, 10 A;20 A, 125/227 V Ac, DPDT Contact Configuration, Solid Brass;Nickel-Plated (Bushing) Material, Screw Connection, Hole Mount, Nickel Plated (Bushing), 1.300 In (L) X 0.760 In (W) X 0.800 In (H), +32 °F Operating Temperature, +185 °F Operating Temperature, 0.11 LB
Weight per unit	N/A
Product Category	Gen Purpose Switches

Features

action	DPDT
amperage rating	20,10
connection	Screw, 6 Terminals
Contact Rating	Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating
operating cycles	100000
Poles	2
Switch Type	Toggle

Dimensions and Weight

Height	0.800
Width	0.760

Descriptions

Description	TOGGLE SWITCH, HEAVY DUTY, DPDT, ON-OFF-ON, SCREW
extra long description	IDEAL 774016 SWITCH,HDTGL,DPDT,O-F-
Features	Great for power tool and motor control switch applicationsRugged long-wearing solid brass/nickel-plated bushings1/2 in. diameter mounting holeDielectric Strength: 1500VMechanical Life: 100,000 cyclesOperating Temperature: 32°F to 185°F (0°C to 85°C)DC?Rating: Factory tested 100,000 cycles to 21 Amp 14.8 VDC

Taxonomies, Classifications, and Categories

Category Description	TOGGLE SWITCHES
Type	Heavy-Duty, On-Off-On

Packaging

Carton	1
Weight Per each	0



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting	1/2 IN Hole Diameter
standard	CSA, RU Listed, RoHS