



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 774093 Toggle Switch, SPST, (O)-F, Screw, 15a

*Ideal*

Catalog Number	774093
Manufacturer	Ideal
Description	Ideal, Toggle Switch, Standard, (On)-Off, Voltage Rating: 125, 227 Vac, Amperage Rating: 20, 10 Amp, Number Of Poles: 1, Action: SPST, Connection: Screw, 2 Terminals, Actuator: Toggle, Contact Rating: Factory Tested 100000 Cycles to 21 Amp 14.8 VDC DC Rating, Size: 1.130 In Length X 0.570 In Width X 0.610 In Height, Mounting: 1/2 In Hole Diameter, Operating Cycles: 100000 Cycles Mechanical Life, Operating Temperature: 32 to 185 Deg F, Dielectric Strength: 1500 V, Finish: Solid Brass/Nickel-Plated Bushings,
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	SPST
actuator	Toggle
amperage rating	10/20
connection	Screw, 2 Terminals
Contact Rating	Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating
operating cycles	100k
Poles	1
Voltage Rating	125/227

### Dimensions and Weight

Size	1.130 IN Length X 0.570 IN Width X 0.610 IN Height
------	--



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	TOGGLE SWITCH, SPST, (O)-F, SCREW, 15A
Features	Great for power tool and motor control switch applications Rugged long-wearing solid brass/nickel-plated bushings 1/2 in. diameter mounting hole Dielectric Strength: 1500V Mechanical Life: 100,000 cycles Operating Temperature: 32°F to 185°F (0°C to 85°C) DC Rating: Factory tested 100,000 cycles to 21 Amp 14.8 VDC
Long Description	IDEAL, Toggle Switch, Standard, (On)-Off, Voltage Rating: 125, 227 VAC, Amperage Rating: 20, 10 AMP, Number Of Poles: 1, Action: SPST, Connection: Screw, 2 Terminals, Actuator: Toggle, Contact Rating: Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating, Size: 1.130 IN Length X 0.570 IN Width X 0.610 IN Height, Mounting: 1/2 IN Hole Diameter, Operating Cycles: 100000 Cycles Mechanical Life, Operating Temperature: 32 To 185 DEG F, Dielectric Strength: 1500 V, Finish: Solid Brass/Nickel-Plated Bushings,
Product Type	Switch, TGL, SPST, (O)-F, SCRW
Special Features	Features: Great For Power Tool And Motor Control Switch Applications; Rugged Long-Wearing Solid Brass/Nickel-Plated Bushings; 1/2 IN Diameter Mounting Hole; Dielectric Strength: 1500 V; Mechanical Life: 100000 Cycles; Operating Temperature: 32 DEG F To 185 DEG F (0 DEG C To 85 DEG C); DC Rating: Factory Tested 100000 Cycles To 21 AMP 14.8 VDC; Bulk Packaging Of 100 Available Upon Request; Dielectric Strength: 1500 V; Finish: Solid Brass/Nickel-Plated Bushings; Hp Rating: 3/4 HP At 125 To 250 VAC

## Manufacturer Information

Brand	Ideal
GTIN	00783250603732
Manufacturers Part Number	774093
UPC	783250603732

## Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Standard, (On)-Off

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	0.15



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	For Power Tool And Motor Control Switch Applications
Mounting	1/2 IN Hole Diameter
Operating Temperature	32 To 185
standard	CSA, RU Listed, RoHS