



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 777211 Indicator Light, Green, 125V, Raised

*Ideal*

|                  |  |
|------------------|--|
| Catalog Number   | 777211   |
| Manufacturer     | Ideal  |
| Description      | Ideal, Indicator Light, Raised, Wattage: 1/3 WTT, Voltage Rating: 125 V, Amperage Rating: 2 Milamp Max, Color: Green Lens, Average Life: 15000 HR, Mounting: 1/2 In Diameter, Operating Temperature: Nylon Body: 140 Deg C, Polycarbonate Lens: 135 Deg C, Bezel: 0.100 In Height, Flammability Rating: 94V-2, Material: Nylon Body With Raised Transparent Polycarbonate Lens and Stainless Steel Bezel, Lamp Type: Neon, Termination Style: 6 In Wire Leads, Lamp Height: 0.200 In |
| Weight per unit  | 0.1000 (lbs/each)  |
| Product Category | Pilot Light Complete Assemblie   |

### Features

|                 |       |
|-----------------|-------|
| amperage rating | 2     |
| average life    | 15000 |
| Voltage Rating  | 125   |
| Wattage         | 1/3   |

### Material, Color, and Finish

|       |            |
|-------|------------|
| Color | Green Lens |
|-------|------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | INDICATOR LIGHT, GREEN, 125V, RAISED   |
| extra long description | IDEAL 777211 Indicator Light,Ideal,  |
| Features               | Nylon body with raised transparent polycarbonate lens and stainless steel bezel, 94V-2 flammability rating1/2 in. mounting diameterLamp voltage is AC/DCOperating Temperature: -- Nylon Body: 140°C -- Polycarbonate lens: 135°C   |
| Long Description       | IDEAL, Indicator Light, Raised, Wattage: 1/3 WTT, Voltage Rating: 125 V, Amperage Rating: 2 MILAMP Max, Color: Green Lens, Average Life: 15000 HR, Mounting: 1/2 IN Diameter, Operating Temperature: Nylon Body: 140 DEG C, Polycarbonate Lens: 135 DEG C, Bezel: 0.100 IN Height, Flammability Rating: 94V-2, Material: Nylon Body With Raised Transparent Polycarbonate Lens And Stainless Steel Bezel, Lamp Type: Neon, Termination Style: 6 IN Wire Leads, Lamp Height: 0.200 IN |
| Product Type           | Indicator Light, Ideal, Raised, Csa, Ul Listed, Vde Certified, 1/3   |
| Special Features       | 1/2 IN Mounting Diameter;Bezel: 0.100 IN Height;Features: Nylon Body With Raised Transparent Polycarbonate Lens And Stainless Steel Bezel, 94V-2 Flammability Rating;Flammability Rating: 94V-2;Lamp Height: 0.200 IN;Lamp Type: Neon;Lamp Voltage Is AC/DC;Material: Nylon Body With Raised Transparent Polycarbonate Lens And Stainless Steel Bezel;Operating Temperature: Nylon Body: 140 DEG C, Polycarbonate lens: 135 DEG C;Termination Style: 6 IN Wire Leads                 |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250606146 |
| Manufacturers Part Number | 777211         |
| UPC                       | 783250606146   |

## Taxonomies, Classifications, and Categories

|                      |                    |
|----------------------|--------------------|
| Category Description | Rotary Disconnects |
| Type                 | RAISED             |

## Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.1 |

## Uses, Certifications, and Standards

|          |                               |
|----------|-------------------------------|
| Mounting | 1/2 IN Diameter               |
| standard | CSA, UL Listed, VDE Certified |