



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



777211 Indicator Light, Green, 125V, Raised

Ideal

| | |
|------------------|--|
| Catalog Number | 777211 |
| Manufacturer | Ideal |
| Description | Ideal, Indicator Light, Raised, Wattage: 1/3 WTT, Voltage Rating: 125 V, Amperage Rating: 2 Milamp Max, Color: Green Lens, Average Life: 15000 HR, Mounting: 1/2 In Diameter, Operating Temperature: Nylon Body: 140 Deg C, Polycarbonate Lens: 135 Deg C, Bezel: 0.100 In Height, Flammability Rating: 94V-2, Material: Nylon Body With Raised Transparent Polycarbonate Lens and Stainless Steel Bezel, Lamp Type: Neon, Termination Style: 6 In Wire Leads, Lamp Height: 0.200 In |
| Weight per unit | 0.1000 (lbs/each) |
| Product Category | Pilot Light Complete Assemblie |

Features

| | |
|-----------------|-------|
| amperage rating | 2 |
| average life | 15000 |
| Voltage Rating | 125 |
| Wattage | 1/3 |

Material, Color, and Finish

| | |
|-------|------------|
| Color | Green Lens |
|-------|------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | INDICATOR LIGHT, GREEN, 125V, RAISED |
| extra long description | IDEAL 777211 Indicator Light,Ideal, |
| Features | Nylon body with raised transparent polycarbonate lens and stainless steel bezel, 94V-2 flammability rating1/2 in. mounting diameterLamp voltage is AC/DCOperating Temperature: -- Nylon Body: 140°C -- Polycarbonate lens: 135°C |
| Long Description | IDEAL, Indicator Light, Raised, Wattage: 1/3 WTT, Voltage Rating: 125 V, Amperage Rating: 2 MILAMP Max, Color: Green Lens, Average Life: 15000 HR, Mounting: 1/2 IN Diameter, Operating Temperature: Nylon Body: 140 DEG C, Polycarbonate Lens: 135 DEG C, Bezel: 0.100 IN Height, Flammability Rating: 94V-2, Material: Nylon Body With Raised Transparent Polycarbonate Lens And Stainless Steel Bezel, Lamp Type: Neon, Termination Style: 6 IN Wire Leads, Lamp Height: 0.200 IN |
| Product Type | Indicator Light, Ideal, Raised, Csa, Ul Listed, Vde Certified, 1/3 |
| Special Features | 1/2 IN Mounting Diameter;Bezel: 0.100 IN Height;Features: Nylon Body With Raised Transparent Polycarbonate Lens And Stainless Steel Bezel, 94V-2 Flammability Rating;Flammability Rating: 94V-2;Lamp Height: 0.200 IN;Lamp Type: Neon;Lamp Voltage Is AC/DC;Material: Nylon Body With Raised Transparent Polycarbonate Lens And Stainless Steel Bezel;Operating Temperature: Nylon Body: 140 DEG C, Polycarbonate lens: 135 DEG C;Termination Style: 6 IN Wire Leads |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250606146 |
| Manufacturers Part Number | 777211 |
| UPC | 783250606146 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Rotary Disconnects |
| Type | RAISED |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.1 |

Uses, Certifications, and Standards

| | |
|----------|-------------------------------|
| Mounting | 1/2 IN Diameter |
| standard | CSA, UL Listed, VDE Certified |