



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 777211 Indicator Light, Green, 125V, Raised

*Ideal*

Catalog Number	777211
Manufacturer	Ideal
Description	Ideal, Indicator Light, Raised, Wattage: 1/3 WTT, Voltage Rating: 125 V, Amperage Rating: 2 Milamp Max, Color: Green Lens, Average Life: 15000 HR, Mounting: 1/2 In Diameter, Operating Temperature: Nylon Body: 140 Deg C, Polycarbonate Lens: 135 Deg C, Bezel: 0.100 In Height, Flammability Rating: 94V-2, Material: Nylon Body With Raised Transparent Polycarbonate Lens and Stainless Steel Bezel, Lamp Type: Neon, Termination Style: 6 In Wire Leads, Lamp Height: 0.200 In
Weight per unit	0.1000 (lbs/each)
Product Category	Pilot Light Complete Assemblie

### Features

amperage rating	2
average life	15000
Voltage Rating	125
Wattage	1/3

### Material, Color, and Finish

Color	Green Lens
-------	------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	INDICATOR LIGHT, GREEN, 125V, RAISED
extra long description	IDEAL 777211 Indicator Light,Ideal,
Features	Nylon body with raised transparent polycarbonate lens and stainless steel bezel, 94V-2 flammability rating1/2 in. mounting diameterLamp voltage is AC/DCOperating Temperature: -- Nylon Body: 140°C -- Polycarbonate lens: 135°C
Long Description	IDEAL, Indicator Light, Raised, Wattage: 1/3 WTT, Voltage Rating: 125 V, Amperage Rating: 2 MILAMP Max, Color: Green Lens, Average Life: 15000 HR, Mounting: 1/2 IN Diameter, Operating Temperature: Nylon Body: 140 DEG C, Polycarbonate Lens: 135 DEG C, Bezel: 0.100 IN Height, Flammability Rating: 94V-2, Material: Nylon Body With Raised Transparent Polycarbonate Lens And Stainless Steel Bezel, Lamp Type: Neon, Termination Style: 6 IN Wire Leads, Lamp Height: 0.200 IN
Product Type	Indicator Light, Ideal, Raised, Csa, Ul Listed, Vde Certified, 1/3
Special Features	1/2 IN Mounting Diameter;Bezel: 0.100 IN Height;Features: Nylon Body With Raised Transparent Polycarbonate Lens And Stainless Steel Bezel, 94V-2 Flammability Rating;Flammability Rating: 94V-2;Lamp Height: 0.200 IN;Lamp Type: Neon;Lamp Voltage Is AC/DC;Material: Nylon Body With Raised Transparent Polycarbonate Lens And Stainless Steel Bezel;Operating Temperature: Nylon Body: 140 DEG C, Polycarbonate lens: 135 DEG C;Termination Style: 6 IN Wire Leads

## Manufacturer Information

Brand	Ideal
GTIN	00783250606146
Manufacturers Part Number	777211
UPC	783250606146

## Taxonomies, Classifications, and Categories

Category Description	Rotary Disconnects
Type	RAISED

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	0.1

## Uses, Certifications, and Standards

Mounting standard	1/2 IN Diameter CSA, UL Listed, VDE Certified
-------------------	--