



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7803MD 30A 3P 3 PH Ac Motor

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 7803MD |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Manual Control Switch, 3 Poles, 30 A, 600 V Ac, 1.7538 (L) X 1.825 (W) X 2.375 (H) In, Box Mount, -40 °C Operating Temperature, +75 °C Operating Temperature, Toggle Actuator, 0.335 LB |
| Weight per unit | 0.3350 (lbs/each) |
| Product Category | Misc Wiring Devices |

Features

| | |
|------------------|-------------------|
| actuator | Toggle |
| amperage rating | 30 |
| connection | Side & Back Wired |
| load | 30A |
| Number of Phases | 3.0 |
| operating cycles | 50000 |
| Poles | 3 Pole |
| Voltage | 600.0 V |
| Wire Size | #14 - #10 Awg |

Dimensions and Weight

| | |
|------|--|
| Size | 1.7538" Depth x 1.825" Width x 2.375" Height |
|------|--|

Descriptions

| | |
|------------------------|--|
| Description | 30A 3P 3 PH AC MOTOR |
| extra long description | P&S 7803MD 30A 3P 3 PH AC MOTOR |
| Special Features | Three Pole, Three Phase AC Manual Motor Controller, suitable as Motor Disconnect |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007267686 |
| Manufacturers Part Number | 7803MD |
| UPC | 785007267686 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------|
| Category Description | POWER TOOLS |
| Type | Manual Controller |

Trade Size

| | |
|----------|------|
| Amperage | 30.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.335 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| environmental conditions | UL94 V2 |
| Frequency Rating | 60Hz |
| Mounting | BOX |
| Operating Temperature | Maximum continuos +75°C, minimum -40°C |
| standard | CULUS, CSA Listed, UL Listed |