


SOCKETS & LAMPHOLDERS

Mogul Base Lampholders

Porcelain—4-5KV Pulse Rated E39 & EX39 Base Pre-Wired

All w/Spring Contacts




80-1791
PINK Glazed
1500W-600V
EX39 Base

Keyless Pink Porcelain Mogul Socket For Protective & Open HID Fixtures, 2 Mounting Screws Held Captive, 1/2" Strip Leads, 2 Wireways - 1 3/8" Center to Center



Cat No.	Leads	Cap	Screw Shell	Master
80-1791	12" 16GA SF-2 B/W 200°	Less	CSSNP	50/1




80-2090
YELLOW Glazed
1500W-600V
E39 Base

Keyless Porcelain Mogul Socket For Position Oriented HID Fixtures w/Body Notch For Correct Mounting, 2 Wireways, 2 Mounting Screws Held Captive - 1 3/8" Center to Center



Cat No.	Leads	Cap	Screw Shell	Master
80-2090	12" 14GA SF-2 B/W 200°	Less	CSSNP	50/1




80-1530
Glazed
1500W-600V
E39 Base

Keyless Porcelain Mogul Socket, Mounting Screw Held Captive, 2 Wireways, 1/2" Strip leads - 1 3/8" Center to Center



Cat No.	Leads	Cap	Screw Shell	Master
80-1530	30" 16GA SF-2 B/W 200°	Less	CSSNP	50/1



80-1377
Glazed
1500W-600V
E39 Base

Keyless Porcelain Mogul Socket, 2 Mounting Screws Held Captive, 2 Wireways, 1/2" Strip Leads, E39 Base - 1 3/8" Center to Center



Cat No.	Leads	Cap	Screw Shell	Master
80-1377	16" 14GA SF-2 B/W 200°	Less	CSSNP 2 #8/32 Screws 2 5/8" H	50/1
80-2030	16" 14GA SF-2 B/W 200°	Less	CSSNP 2 #8/32 Screws 3" H	50/1
80-2031	16" 14GA SF-2 B/W 200°	Less	CSSNP 2 #8/32 Bushings 3" H	50/1

Metal Caps w/Set Screw



80-1631
1/4 IP



80-1665
3/8 IP