



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



804DCI2 1/2" 90D Diecast Ins Conn *Bridgeport Fittings*

| | |
|------------------|---|
| Catalog Number | 804DCI2 |
| Manufacturer | Bridgeport Fittings |
| Description | Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1/2 Inch |
| Weight per unit | 0.1352 (lbs/each) |
| Product Category | Liquid Tight Fittings |

Features

| | |
|----------------------|---------------|
| angle | 90 DEG |
| Connector Type | FMC |
| Material | Zinc Die Cast |
| media | Yes |
| Number of Conductors | 1 Cable |

Material, Color, and Finish

| | |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

Dimensions and Weight

| | |
|------|-----|
| Size | 1/2 |
|------|-----|

Descriptions

| | |
|------------------------|---|
| Description | 1/2" 90D DIECAST INS CONN |
| extra long description | BPT 804-DCI2 1/2" 90 DEG CONN. INS. |
| Long Description | Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1/2 Inch |
| Product Type | 1/2" 90 Deg Conn. Ins. Zinc |
| Special Features | Furnished with 2-way Phillips/Slotted Head Screw |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Bridgeport Fittings |
| GTIN | 00781747168047 |
| Manufacturers Part Number | 804-DCI2 |
| UPC | 781747168047 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | FLEX & MC FITTINGS |
| Type | CONNECTOR |

Trade Size

| | |
|------------|-----|
| Trade Size | 1/2 |
|------------|-----|

Packaging

| | |
|-----------------|--------|
| Carton | 25 |
| Package | 100 |
| Weight Per each | 0.1352 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Application | 90 Degrees connector suitable for use to connect MC/FMC to box or enclosure. Insulator rated 105 degrees C. Diameter (.75" 0 min) (.875" 0 max) |
| standard | UL, CSA |
| Temperature Rating | 105°C |