



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 804DCI2 1/2" 90D Diecast Ins Conn *Bridgeport Fittings*

Catalog Number	804DCI2
Manufacturer	Bridgeport Fittings
Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1/2 Inch
Weight per unit	0.1352 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

angle	90 DEG
Connector Type	FMC
Material	Zinc Die Cast
media	Yes
Number of Conductors	1 Cable

### Material, Color, and Finish

Finish	Ball burnish
--------	--------------

### Dimensions and Weight

Size	1/2
------	-----

### Descriptions

Description	1/2" 90D DIECAST INS CONN
extra long description	BPT 804-DCI2 1/2" 90 DEG CONN. INS.
Long Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1/2 Inch
Product Type	1/2" 90 Deg Conn. Ins. Zinc
Special Features	Furnished with 2-way Phillips/Slotted Head Screw

### Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747168047
Manufacturers Part Number	804-DCI2
UPC	781747168047

### Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

### Trade Size

Trade Size	1/2
------------	-----

### Packaging

Carton	25
Package	100
Weight Per each	0.1352



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	90 Degrees connector suitable for use to connect MC/FMC to box or enclosure. Insulator rated 105 degrees C. Diameter (.75" 0 min) (.875" 0 max)
standard	UL, CSA
Temperature Rating	105°C