



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



807DCI2 1" 90D Diecast Ins Conn *Bridgeport Fittings*

Catalog Number	807DCI2
Manufacturer	Bridgeport Fittings
Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1 Inch
Weight per unit	0.3720 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	90 DEG
Connector Type	FMC
Material	Zinc Die Cast
media	Yes
Number of Conductors	1 Cable

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	1
------	---

Descriptions

Description	1" 90D DIECAST INS CONN
extra long description	BPT 807-DCI2 1" ANGLE CONN. INS. ZI
Long Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1 Inch
Product Type	1" Angle Conn. Ins. Zinc
Special Features	Furnished with 2-way Phillips/Slotted Head Screw

Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747168078
Manufacturers Part Number	807-DCI2
UPC	781747168078

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	1
------------	---

Packaging

Carton	25
Weight Per each	0.372



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	90 Degrees connector suitable for use to connect MC/FMC to box or enclosure. Insulator rated 105 degrees C. 1.187" 0 min to 1.312" 0 max
standard	UL, CSA
Temperature Rating	105°C