



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



808DCI2 1-1/4" 90D Diecast Ins Conn *Bridgeport Fittings*

Catalog Number	808DCI2
Manufacturer	Bridgeport Fittings
Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1 1/4 Inch
Weight per unit	0.6480 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	90 DEG
Connector Type	FMC
Material	Zinc Die Cast
media	Yes
Number of Conductors	1 Cable

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	1-1/4
------	-------

Descriptions

Description	1-1/4" 90D DIECAST INS CONN
extra long description	BPT 808-DCI2 1-1/4" ANGLE CONN. INS
Long Description	Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 1 1/4 Inch
Product Type	1-1/4" Angle Conn. Ins. Zinc
Special Features	Furnished with 2-way Phillips/Slotted Head Screw

Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747168085
Manufacturers Part Number	808-DCI2
UPC	781747168085

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	1-1/4
------------	-------

Packaging

Carton	25
Weight Per each	0.648



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	90 Degrees connector suitable for use to connect flexible metal conduit to box or enclosure. Insulator rated 105 degrees C. Diameter for 1.500" 0 min to 1.625" 0 max.
standard	UL, CSA
Temperature Rating	105°C