



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8300RED Hosp GRD Dup Recept 20A/125VAC Red

Pass & Seymour/Legrand

Catalog Number	8300RED
Manufacturer	Pass & Seymour/Legrand
Description	Extra Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V
Weight per unit	0.2500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon;Other
Number of Wires	3
Outlet Type	Indoor, Commercial
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Color	Red
Finish	Matte

Dimensions and Weight

Height	3.281
Width	.900



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	HOSP GRD DUP RECEPT 20A/125VAC RED
extra long description	P&S 8300RED HOSP GRD DUP RECEPT 20A
Long Description	Extra Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V
Product Type	Hosp GRD Dup Recept 20A/125VAC Red
Special Features	One-piece nickel-plated brass mounting strap with integral ground. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Two drive screws anchor strap to back body and face. Exclusive patented feature, circuit label on face allows permanent circuit identification. .040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007830101
Manufacturers Part Number	8300RED
UPC	785007830101

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.25

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2 and UL94-5 VA
Mounting	WALL
nema rating	5-20R
standard	CULUS, FEDSPEC, cULus UL498, CSA C22.2 No. 42
Temperature Rating	-40° - 60° C