



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8300STW Edge, Pro RCPT, HG, 20A 125V, WH Hubbell Wiring Devices

Catalog Number	8300STW
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Edgeconnect™, Hubbell-Pro Receptacle, Hospital Grade, 2-Pole 3-Wire, 20A 125V, 5-20R, Screwless Terminal, White
Weight per unit	0.2000 (lbs/each)
Product Category	Wiring Devices

Features

connection	2-Pole, 3 Wire
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wire Size	#14 to #10

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	EDGE, PRO RCPT, HG, 20A 125V, WH
extra long description	HWDK 8300STW EDGE, PRO RCPT, HG, 20
Features	EdgeConnect™ Screwless Termination system, simply insert the wire and press the plunger down. No tools are required. That connection is fool-proof and long lasting, to all but guarantee a high quality result. Any qualified installer regardless of level of training can guarantee a high quality result. Elapsed time? About 11 seconds!
Long Description	Straight Blade Devices, EdgeConnect™, Hubbell-Pro Receptacle, Hospital Grade, 2-Pole 3-Wire, 20A 125V, 5-20R, Screwless Terminal, White
Product Type	Edge, Pro RCPT, HG, 20A 125V, WH
Special Features	EdgeConnect™ Technology, Screwless Termination

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585726953
Manufacturers Part Number	8300STW
series	EdgeConnect™
UPC	783585726953



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Hospital Grade

Packaging

Carton	1
Package	10
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Hubbell-PRO
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA 22.2, No. 42 File 285; Fed. Spec. W-C-596, NEMA® WD-6 Compliant; UL Listed to UL498 File No. E2186