



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



85334 2.4 GHz 4-Way Satellite & Digital TV Splitter

Ideal

Catalog Number	85334
Manufacturer	Ideal
Description	Ideal, Splitter, Frequency Range: 2 GHz, Connector: F Female, Includes: Two Mounting Screws (Phillips/Slotted Head)
Weight per unit	0.2500 (lbs/each)
Product Category	Couplers, SPLITTERS, Switches, Att

Features

connector	F Female
Frequency Range	2

Descriptions

Description	2.4 GHz 4-WAY SATELLITE & DIGITAL TV SPLITTER
extra long description	IDEAL 85-334 4-WAY 2 GHz SPLITTER
Features	High performance 2.4 GHz Digital Splitters are used for splitting a single coax line into 2, 3, or 4 lines. These splitters are designed for applications that operate in the 5 MHz to 2.4 GHz range, which include: Satellite, Digital/HD Cable TV, Broadcast (over the air) TV, CCTV, and other general purpose coaxial cable splitting requirements. Splitters support the 1 Ghz to 2.4 GHz frequency range for satellite and on-demand cable television services.
Long Description	IDEAL, Splitter, Frequency Range: 2 GHz, Connector: F Female, Includes: Two Mounting Screws (Phillips/slotted head)
Product Type	4-Way 2 GHz Splitter
Special Features	Features: Designed for easy mounting over cable; All ports are F female connectors; Two grounding screws eliminate the need for grounding block; Includes two mounting screws (Phillips/slotted head); Includes: Two Mounting Screws (Phillips/slotted head)

Manufacturer Information

Brand	Ideal
GTIN	00783250853342
Manufacturers Part Number	85-334
UPC	783250853342

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	--

Packaging

Carton	1
Weight Per each	0.25

Uses, Certifications, and Standards

Application	Splitting of Satellite and Digital Cable Signal on F Type coax runs
-------------	---