



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



85340 3GHZ F-Type Femi-to-Femi Coax Splice Adptry 10/Card

Ideal

Catalog Number	85340
Manufacturer	Ideal
Description	Ideal 85-340 F-Splice Adapter, Connection: F
Weight per unit	0.2000 (lbs/each)
Product Category	Connecting Devices - Adapters

Features

connection	F
------------	---

Descriptions

Description	3GHZ F-TYPE FEML-TO-FEML COAX SPLICE ADPTR 10/CARD
extra long description	IDEAL 85-340 3GHZ F-81 FEM SPLICE A
Features	Use the 3GHz F-Splice Adapter for extending coaxial cable runs for all cable and satellite TV applications including High Definition. Attach F-connectors to both ends of the barrel splice to join the cables together. Best for High Definition applications. Nickel plated brass construction. For 750 applications up to 3GHz. Accepts male F connectors on both sides. High bandwidth 0MHz to 3GHz for standard and high definition applications. Long body style for wallplate upgrades. < 0.25 dB insertion loss to maintain signal strength.
Long Description	Ideal 85-340 F-Splice Adapter, Connection: F
Product Type	3GHZ F-81 Fem Splice Adpt 10PK
Special Features	High bandwidth; 0 MHz - 3 GHz for standard and high definition applications; Less than 0.25 DB insertion loss, greater than 25 DB return loss

Manufacturer Information

Brand	Ideal
GTIN	00783250853403
Manufacturers Part Number	85-340
UPC	783250853403

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	F-Splice Adapter

Availability

minimum qty	10
-------------	----

Packaging

Carton	10
Weight Per each	0.2