

---

## MOGUL BASE LAMPHOLDER

8694 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Mogul Base, porcelain, screw terminals, keyless, single pole with bushings, 4kv pulse rated. White.



- Quality Materials.
- Durability.
- Time-tested design.

---

### SPECIFICATIONS

#### GENERAL INFO

Type: Incandescent Mogul Base Lampholder

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39111803  
UR: No

#### DIMENSIONS

Diameter (US): 2.13"  
Height: 2.56"

#### TECHNICAL INFORMATION

Volts: 600V  
Volts (AC): 600  
Watts: 1500

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA  
Buy American Act Status: No

---

## MOGUL BASE LAMPHOLDER

8694 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Mogul Base, porcelain, screw terminals, keyless, single pole with bushings, 4kv pulse rated. White.



- Quality Materials.
- Durability.
- Time-tested design.

---

### SPECIFICATIONS

#### GENERAL INFO

Type: Incandescent Mogul Base Lampholder

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39111803  
UR: No

#### DIMENSIONS

Diameter (US): 2.13"  
Height: 2.56"

#### TECHNICAL INFORMATION

Volts: 600V  
Volts (AC): 600  
Watts: 1500

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA  
Buy American Act Status: No