



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 8836GNK 8X8X36 Wireway

Unity MFG

Catalog Number	8836GNK
Manufacturer	Unity MFG
Description	Unity 8836GNK Lay-In Wireway, Removable Hinged Cover Type, Length: 36 In, Width: 8 In, 8 In Height, Nema 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 14 Ga Low Carbon Steel, Gunsmoke Gray Powder Coated, No Knockouts, C/Us UI 50 and UI 870 - Type 1: Intended For Indoor Use Primarily to Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, Csa C22.2 No. 26 Certified, Type 1, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and Termination, H
Weight per unit	19.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

### Features

Cover Type	Removable Hinged
Knockouts	NO
Material	Low-Carbon Steel

### Material, Color, and Finish

Finish	Powder Coat
--------	-------------

### Dimensions and Weight

Height	8
Length	36
Width	8



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Construction	Formed From Code Gauge, Low Carbon Steel
Description	8X8X36 WIREWAY
extra long description	UNT 8836GNK N1 HINGED COVER WIREWAY
Long Description	Unity 8836GNK Lay-In Wireway, Removable Hinged Cover Type, Length: 36 IN, Width: 8 IN, 8 IN Height, NEMA 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 14 GA Low Carbon Steel, Gunsmoke Gray Powder Coated, No Knockouts, C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And Termination, H
Product Type	N1 Hinged Cover Wireway No K.O. Powder Coated
Special Features	For protecting electrical wiring where dust, dirt, oil and water are not serious problems; All sections and fittings are fully open on one side so wires and cables can be laid in along an entire run; No pulling-through of wires or cables is required; Wireway body has mounting holes on the back; Cover is secured to the body with plated screws; Keyhole slots are furnished on the wireway cover which allow easy access to the inside without removing the screws

## Manufacturer Information

Brand	Unity
GTIN	00761515104309
Manufacturers Part Number	8836GNK
UPC	761515104309

## Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Lay-In Wireway

## Packaging

Carton	1
Weight Per each	19



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Cable And Wire Junction, Distribution And Termination,  
Houses Runs Of Control And Power Cable

Enclosure  
standard

NEMA 1, IP30

C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use  
Primarily To Provide A Degree Of Protection Against Limited  
Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC  
60529, RoHS Compliant