



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8836GNK 8X8X36 Wireway *Unity Manufacturing*

Catalog Number	8836GNK
Manufacturer	Unity Manufacturing
Description	Unity 8836GNK Lay-In Wireway, Removable Hinged Cover Type, Length: 36 In, Width: 8 In, 8 In Height, Nema 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 14 Ga Low Carbon Steel, Gunsmoke Gray Powder Coated, No Knockouts, C/Us UI 50 and UI 870 - Type 1: Intended For Indoor Use Primarily to Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, Csa C22.2 No. 26 Certified, Type 1, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and Termination, H
Weight per unit	19.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

Cover Type	Removable Hinged
Knockouts	NO
Material	Low-Carbon Steel

Material, Color, and Finish

Finish	Powder Coat
--------	-------------

Dimensions and Weight

Height	8
Length	36
Width	8



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	Formed From Code Gauge, Low Carbon Steel
Description	8X8X36 WIREWAY
extra long description	UNT 8836GNK N1 HINGED COVER WIREWAY
Long Description	Unity 8836GNK Lay-In Wireway, Removable Hinged Cover Type, Length: 36 IN, Width: 8 IN, 8 IN Height, NEMA 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 14 GA Low Carbon Steel, Gunsmoke Gray Powder Coated, No Knockouts, C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And Termination, H
Product Type	N1 Hinged Cover Wireway No K.O. Powder Coated
Special Features	For protecting electrical wiring where dust, dirt, oil and water are not serious problems; All sections and fittings are fully open on one side so wires and cables can be laid in along an entire run; No pulling-through of wires or cables is required; Wireway body has mounting holes on the back; Cover is secured to the body with plated screws; Keyhole slots are furnished on the wireway cover which allow easy access to the inside without removing the screws

Manufacturer Information

Brand	Unity
GTIN	00761515104309
Manufacturers Part Number	8836GNK
UPC	761515104309

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Lay-In Wireway

Packaging

Carton	1
Weight Per each	19



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Cable And Wire Junction, Distribution And Termination,
Houses Runs Of Control And Power Cable

Enclosure
standard

NEMA 1, IP30

C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use
Primarily To Provide A Degree Of Protection Against Limited
Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC
60529, RoHS Compliant