



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



885TRDBCC12 Radiant 15A/125V TR Duplex Recept DB CC12

Pass & Seymour/Legrand

Catalog Number	885TRDBCC12
Manufacturer	Pass & Seymour/Legrand
Description	Take A Step Up From The Standard. This Tamper-Resistant Duplex Outlet Installs Easily For The Basic Power Every Home Needs, While Elevating Your Space With The Sleek, Clean Lines Of Radiant Registered For A Sophisticated Look. Made Exclusively For Use With Screwless Wall Plates From The Radiant Registered Collection, Sold Separately.
Weight per unit	0.1667 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

indoor/outdoor	Indoor
Mounting Type	Box
Outlet Type	Tamper-Resistant
Poles	2
Voltage	125.0 V

Material, Color, and Finish

Finish	Metallic
--------	----------

Descriptions

Description	RADIANT 15A/125V TR DUPLEX RECP DB CC12
extra long description	P&S 885TRDBCC12 RADIANT 15A/125V TR
Long Description	Take a step up from the standard. This tamper-resistant duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant Registered for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.
Product Type	Radiant 15A/125V TR Dup Recept DB CC12

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007029413
Manufacturers Part Number	885-TRDBCC12
UPC	785007029413

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Outlet

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	12
Weight Per each	0.1667

Uses, Certifications, and Standards

environmental conditions	95% (relative humidity, non-condensing)
nema rating	15A
standard	CULUS, UL