



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 8872GNK 8X8X72 Wireway

Unity MFG

|                  |   |
|------------------|---|
| Catalog Number   | 8872GNK   |
| Manufacturer     | Unity MFG   |
| Description      | Unity 8872GNK Lay-In Wireway, Removable Hinged Cover Type, Length: 72 In, Width: 8 In, 8 In Height, Nema 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 14 Ga Low Carbon Steel, Gunsmoke Gray Powder Coated, No Knockouts, C/Us UI 50 and UI 870 - Type 1: Intended For Indoor Use Primarily to Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, Csa C22.2 No. 26 Certified, Type 1, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and Termination, H |
| Weight per unit  | 39.0 (lbs/each)   |
| Product Category | Nema Type 1 Wireway & Fittings  |

### Features

|            |                  |
|------------|------------------|
| Cover Type | Removable Hinged |
| Knockouts  | NO               |
| Material   | Low-Carbon Steel |

### Material, Color, and Finish

|        |             |
|--------|-------------|
| Finish | Powder Coat |
|--------|-------------|

### Dimensions and Weight

|        |    |
|--------|----|
| Height | 8  |
| Length | 72 |
| Width  | 8  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Construction           | Formed From Code Gauge, Low Carbon Steel  |
| Description            | 8X8X72 WIREWAY  |
| extra long description | UNT 8872GNK N1 HINGED COVER WIREWAY   |
| Long Description       | Unity 8872GNK Lay-In Wireway, Removable Hinged Cover Type, Length: 72 IN, Width: 8 IN, 8 IN Height, NEMA 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 14 GA Low Carbon Steel, Gunsmoke Gray Powder Coated, No Knockouts, C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And Termination, H |
| Product Type           | N1 Hinged Cover Wireway No K.O. Powder Coated   |
| Special Features       | For protecting electrical wiring where dust, dirt, oil and water are not serious problems; All sections and fittings are fully open on one side so wires and cables can be laid in along an entire run; No pulling-through of wires or cables is required; Wireway body has mounting holes on the back; Cover is secured to the body with plated screws; Keyhole slots are furnished on the wireway cover which allow easy access to the inside without removing the screws; #10-32 x 5/16 thread forming screw                 |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Unity          |
| GTIN                      | 00761515104606 |
| Manufacturers Part Number | 8872GNK        |
| UPC                       | 761515104606   |

## Taxonomies, Classifications, and Categories

|                      |                               |
|----------------------|-------------------------------|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type                 | Lay-In Wireway                |

## Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 39 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Cable And Wire Junction, Distribution And Termination,  
Houses Runs Of Control And Power Cable

Enclosure  
standard

NEMA 1, IP30

C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use  
Primarily To Provide A Degree Of Protection Against Limited  
Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC  
60529, RoHS Compliant