



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 89048 Insite RTQ RG-6 BNC Comp Conn, 15/Card

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | 89048   |
| Manufacturer     | Ideal   |
| Description      | Ideal, Compression Connector, BNC, Conductor Range: 029 - 042 In, 20 - 18 Awg Solid Center Conductor, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 Ohm, Dielectric Diameter: 0.175 - 0.183 In, Coaxial Cable Type: RG-6, Overall Jacket Diameter: 0.260 - 0.305 In |
| Weight per unit  | 0.0030 (lbs/each)   |
| Product Category | Coaxial & Twinaxial Connectors  |

### Features

|          |       |
|----------|-------|
| Material | Brass |
|----------|-------|

### Material, Color, and Finish

|        |               |
|--------|---------------|
| Finish | Nickel-Plated |
|--------|---------------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | INSITE RTQ RG-6 BNC COMP CONN, 15/CARD  |
| extra long description | IDEAL 89-048 RG6 BNC COMPR CONN 15  |
| Features               | Connector Model: 6BNCISRTQAccepts RG-6/RG-6 Quad/RG-6 Plenum/RG-6 Plenum Quad coax cablesCenter conductor range: 23-18 AWG Solid (.023" - .040")Dielectric diameter range: .168" - .183"Outer jacket diameter range: .226" - .305"Connector Model: 6BNCISRTQAccepts RG-6/RG-6 Quad/RG-6 Plenum/RG-6 Plenum Quad coax cablesCenter conductor range: 23-18 AWG Solid (.023" - .040")Dielectric diameter range: .168" - .183"Outer jacket diameter range: .226" - .305"Recommended cable prep/stripping tools: 45-605 PrepPRORecom |
| Long Description       | IDEAL, Compression Connector, BNC, Conductor Range: 029 - 042 IN, 20 - 18 AWG Solid Center Conductor, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 OHM, Dielectric Diameter: 0.175 - 0.183 IN, Coaxial Cable Type: RG-6, Overall Jacket Diameter: 0.260 - 0.305 IN   |
| Product Type           | RG6 BNC Compr Conn 15 CD  |
| Special Features       | Features: Nickel-Plated, Brass-Construction For Superior Corrosion Resistance; Moisture-Inhibiting Design; Approved For Indoor And Outdoor Use; Use 30-793 Compression Tool; 75 OHM Nominal Impedance; Gold-Plated Pin Contact Area; Available In Plenum Versions; Nominal Impedance: 75 OHM; Dielectric Diameter: 0.175 - 0.183 IN; Coaxial Cable Type: RG-6; Overall Jacket Diameter: 0.260 - 0.305 IN  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250890484 |
| Manufacturers Part Number | 89048          |
| UPC                       | 783250890484   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
| Type                 | BNC                                    |

## Availability

|             |    |
|-------------|----|
| minimum qty | 15 |
|-------------|----|

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 15    |
| Weight Per each | 0.003 |

## Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | For CCTV System Installations/Integrations And General Purpose Applications on RG 6 Cable |
|-------------|---|