


8908 Series

120V-60Hz

Catalog #:		Type
Project:		Date
Prepared by:		

LED Mini Step Light



LED Mini Step Light

DESCRIPTION

The 8908 Series Mini LED Step Light is a easy-to-install low profile fixture that produces an attractive glow. Ideal for lighting low light areas such as corridors or pathways, and can be mounted vertically or horizontally.

DESIGN FEATURES

Construction

- IC rated for direct contact w/ insulation
- Horizontal and vertical louvered front cover included

Electrical

- 120V-60Hz
- 50,000 hour projected life
- LED
- 1Watt
- Available in 3500K
- CRI 80

Dimensions

- Height 4.5" x Width 2.75"

Finish

- Available in White, brushed aluminum, and light almond

Certifications

- UL listed for damp location
- 5 year limited warranty

ORDERING		Example: 8908WW	
Model #	Finish		
8908			
8908	BA LAL WW	:	Brushed Aluminum Light Almond White





8908 Series

120V-60Hz

Catalog #:		Type
Project:		Date
Prepared by:		

LED Mini Step Light



LED Mini Step Light

DESCRIPTION

The 8908 Series Mini LED Step Light is a easy-to-install low profile fixture that produces an attractive glow. Ideal for lighting low light areas such as corridors or pathways, and can be mounted vertically or horizontally.

DESIGN FEATURES

Construction

- IC rated for direct contact w/ insulation
- Horizontal and vertical louvered front cover included

Electrical

- 120V-60Hz
- 50,000 hour projected life
- LED
- 1Watt
- Available in 3500K
- CRI 80

Dimensions

- Height 4.5" x Width 2.75"

Finish

- Available in White, brushed aluminum, and light almond

Certifications

- UL listed for damp location
- 5 year limited warranty

ORDERING		Example: 8908WW		
Model #	Finish			
8908				
8908	BA	:	Brushed Aluminum	
	LAL			Light Almond
	WW			White

