



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



891545 Omniconn RG-6 Quad F Compr Conn Black, 1, 000/Box

Ideal

Catalog Number	891545
Manufacturer	Ideal
Description	Ideal, Compression Connector, Omniconn, F-Type, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 Ohm, Ports Size: 7/16 In, Coaxial Cable Type: RG-6, Bandwidth: 3 GHZ, Dielectric Diameter: 0.175 - 0.183 In, Overall Jacket Diameter: 0.260 - 0.280 In
Weight per unit	17.4 (lbs/each)
Product Category	Coaxial & Twinaxial Connectors

Features

Material	Brass
----------	-------

Material, Color, and Finish

Finish	Nickel-Plated
--------	---------------

Descriptions

Description	OMNICONN RG-6 QUAD F COMPR CONN BLACK, 1,000/BOX
extra long description	IDEAL 89-1545 RG6 QUAD CMPR,PLSTC,1
Features	Connector Model: 6QFOCAccepts RG-6 Quad coax cablesCenter conductor range: AllDielectric diameter range: .175" - .183"Outer jacket diameter range: .270" - .295"Recommended cable prep/stripping tools: 45-605 PrepPRO; 45-526Recommended compression tools: 30-793 OmniSeal PRO XL; 33-632 Linear X3The IDEAL OmniConn F connector is a cable specific connector solution for RG-6 coax. The OmniConn connectors have a combination brass and plastic exterior and an inner O-ring to provide a weather proof connection suita
Long Description	IDEAL, Compression Connector, OmniCONN, F-Type, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 OHM, Ports Size: 7/16 IN, Coaxial Cable Type: RG-6, Bandwidth: 3 GHZ, Dielectric Diameter: 0.175 - 0.183 IN, Overall Jacket Diameter: 0.260 - 0.280 IN
Product Type	RG6 Quad CMPR, PLSTC, 1000 Bulk
Special Features	Features: Omniconn F Compression Connectors Install Easily Onto Standard RG 6 And RG 6Quad Cables; Non Corrosive Nickel Plated Brass Body And Polycarbonate Bushing; Delrin/Nylon Adapter Sleeve And O-Ring Provide Double Protection For A Watertight Seal; Free Spinning Hex Nut For Ease Of Installation Onto All 7/16 IN Ports 75 OHM Nominal Impedance; Bandwidth Up To 3 GHZ; Two-Piece Pre-Assembled Connectors; Nominal Impedance: 75 OHM; Ports Size: 7/16 IN; Coaxial Cable Type: RG-6; Bandwidth: 3 GHZ; Dielectric



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Ideal
GTIN	00783250681723
Manufacturers Part Number	89-1545
UPC	783250681723

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	F-Type

Availability

minimum qty	1000
-------------	------

Packaging

Carton	1000
Weight Per each	17.4

Uses, Certifications, and Standards

Application	Terminating an F Style connection onto RG 6 Quad Coax .
-------------	---