



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



89608 Barrier Strip, 12-Circuit

Ideal

| | |
|------------------|---|
| Catalog Number | 89608 |
| Manufacturer | Ideal |
| Description | Barrier Strip, 12 Circuits, 8 Poles, 20 A, 300/400 V, Plastic, +221 °F, 3.787 In Overall Length, 0.669 In Overall Width, 0.570 In Overall Height, 0.11 LB |
| Weight per unit | 0.1070 (lbs/each) |
| Product Category | Power BLKS & Distribution BLKS |

Features

| | |
|-----------------|-----------------|
| amperage rating | 20, 10 |
| Material | Plastic Housing |
| Voltage Rating | 300, 400 |
| Wire Size | 22 - 12 |

Descriptions

| | |
|------------------------|--|
| Description | BARRIER STRIP, 12-CIRCUIT |
| extra long description | IDEAL 89-608 TERMINAL BLOCK 12 POLE |
| Features | IDEAL Barrier Strips are designed and manufactured to be rugged, reliable, and easy to use. A thermoplastic base and corrosion-resistant screws and hardware provide extended service life. |
| Special Features | Features: UL Recognized For 20A, 300V; CSA Certified For 10A, 400V; Torque Rating Of 3.5 In-Lbs; Recessed Screws And Tubular Contacts; UL Listed And CSA Certified; Connect Stripped Un-Terminated Solid Or Stranded Wire; Modular 12 Circuits Can Be Cut Into Smaller Sections; Plastic Housing Is UL Flame Rated To 94V-2; Rated Temperature To 105 Degrees C; Recessed Screws And Tubular Contacts Provide Added Safety And Help Prevent Short Circuits; Tubular Contacts Connect Stripped, Un-Terminated Solid Or Stranded |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Ideal |
| GTIN | 00783250896080 |
| UPC | 783250896080 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
|----------------------|--|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 0.107 |

Uses, Certifications, and Standards

| | |
|----------|----------------------|
| standard | C/US UL Listed, RoHS |
|----------|----------------------|