



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8TSNLEDLD596S840 8tsnledld596slunvl840cd1 *Cooper Lighting Solutions*

Catalog Number	8TSNLEDLD596S840
Manufacturer	Cooper Lighting Solutions
Description	Led Striplight, 120 to 277 V, 0.25 A @ 277 V, 69.2 W, Cold Rolled Steel, 4000 K, 80, >60000 H Average Life, Dimmable, 9632 LM Brightness (Lumens), 96 In Length, 1-25/32 In Width, 2-7/8 In Height, 13.1 LB
Weight per unit	11.3 (lbs/each)
Product Category	Led Surface Architectural & SP

Features

amperage rating	0.25 (at277V)
Lamp Type	LED
lumens	9600
Number of Lamps	1
Wattage	69 W

Dimensions and Weight

Size	96.25 IN Length 3.313 IN Width 2.375 IN Height
------	--

Descriptions

Description	8TSNLEDLD596SLUNVL840CD1
extra long description	CLS 8TSNLED-LD5-96SL-UNV-L840-CD1-U

Manufacturer Information

Brand	METALUX COMMERCIAL
GTIN	00080083803392
UPC	080083803392

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Strip

Packaging

Carton	1
Weight Per each	11.3

Uses, Certifications, and Standards

Mounting	Surface Mount
standard	UL/cUL Listed - Damp Location;RoHS Compliant