



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8TVT3232DRUNVEB8 8' Tandem T8 Vaportite Fixture

Cooper Lighting Solutions

Catalog Number	8TVT3232DRUNVEB8
Manufacturer	Cooper Lighting Solutions
Description	(4) 32W T8 8' Tandem Instant Start Cee Listed Ballast, 120-277V, Wet Location, Gear Tray Provided With Holes For M4 Reflector Accessory
Weight per unit	17.2 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.22 at (277V)
Ballast Type	INSTANT START ELECTRONIC
Fixture Type	Industrial
Lamp Type	T8
Material	Fiberglass
Number of Lamps	2
Shape	Rectangular
Voltage Rating	120-277V

Descriptions

Description	8' TANDEM T8 VAPORTITE FIXTURE
extra long description	CLS 8TVT3-232DR-UNV-EB81-WL-GT4-U V
Long Description	(4) 32W T8 8' Tandem Instant Start CEE Listed Ballast, 120-277V, Wet Location, Gear Tray Provided With Holes For M4 Reflector Accessory
Product Type	VT3 8' VPRT (4) 32W T8 Cee Wet M4 Ready
Special Features	Maximum operation in commercial and industrial environments

Manufacturer Information

Brand	Cooper Metalux
GTIN	00080083534319
Manufacturers Part Number	8TVT3-232DR-UNV-EB81-WL-GT4-U
UPC	080083534319

Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Vapor Tite

Packaging

Carton	1
Weight Per each	17.2099



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application lighting
standard UL/cUL Listed - Wet Location