



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



90085 Screw Point Flexible Bit 1/2" X 54"

Ideal

Catalog Number	90085
Manufacturer	Ideal
Description	Ideal, Flexible Bit, Screw Point, Type B, Bit Diameter: 1/2 In, Overall Length: 54 In, Shank Diameter: 3/16 In
Weight per unit	0.6000 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Shank Diameter	3/16
----------------	------

Dimensions and Weight

Overall Length	54
----------------	----

Descriptions

Description	SCREW POINT FLEXIBLE BIT 1/2" X 54"
extra long description	IDEAL 90-085 Flexible Bit,Ideal,SCR
Features	Fast and aggressive, self-starting bitUltra-sharp ground threads provide increased pulling power through obstructionsDesigned for easy to tough wood
Long Description	IDEAL, Flexible Bit, Screw Point, Type B, Bit Diameter: 1/2 IN, Overall Length: 54 IN, Shank Diameter: 3/16 IN
Product Type	Flexible Bit, Ideal, SCR Point, Type B, 1/2 In Bit Diameter, 54.0
Special Features	Features: Fast And Aggressive, Self-Starting Bit; Ultra-Sharp Ground Threads Provide Increased Pulling Power Through Obstructions; Designed For Easy To Tough Wood Drilling

Manufacturer Information

Brand	Ideal
GTIN	00783250900855
Manufacturers Part Number	90085
UPC	783250900855

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Screw Point, Type B

Packaging

Carton	2
Weight Per each	0.6

Uses, Certifications, and Standards

Application	For Easy To Tough Wood Drilling
standard	RoHS