

**9120**  
120-volt AC  
Smoke Alarm

- 120-volt AC
- Single Button Silence/Test
- Tamper-Resistant Locking Pins
- Universal Mounting Bracket
- Latching Alarm Indication
- 10-Year Limited Warranty



**9120B**  
120-volt AC Smoke Alarm  
with Battery Backup

- 120-volt AC with 9V Battery Backup
  - Single Button Silence/Test
  - Tamper-Resistant Locking Pins
  - Universal Mounting Bracket
  - Side-Load Battery Drawer
  - Latching Alarm Indication
  - 10-Year Limited Warranty
- Also available in clamshell: SA9120BCN



**RM4**  
Relay

- Activates auxiliary devices like a bell, siren, strobe light, exhaust fan, alarm panel, or door closer when connected alarm is activated
- 120-volt AC
- Form C contacts switch between a normally open contact a normally closed contact
- Maximum contact range: 120-volt AC and 30 volt DC; Resistive-15
- Fits in most standard junction boxes



**100S**  
120-volt AC Hearing  
Impaired Smoke Alarm

- Meets requirements of the ADA (Americans with Disabilities Act)
- 177-Candela Strobe Light
- 120-volt AC
- Test Button
- 10-Year Limited Warranty



**HD6135FB**  
120-volt AC Heat Alarm  
with Battery Backup

- 135°F fixed and 15°F/min rate-of-rise heat alarm
- 120-volt AC with 9V Battery Backup
- Single Button Silence/Test
- Tamper-Resistant Locking Pins
- Universal Mounting Bracket
- Side-Load Battery Drawer
- Latching Alarm Indication
- Dust Cover
- Interconnectable with BRK® and First Alert® hardwired smoke and CO alarms
- 10-Year Limited Warranty

