



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## 91609 3/16" High Speed Jobber Drill, 118 Point, Steel

*Minerallac Company*

Catalog Number	91609
Manufacturer	Minerallac Company
Description	3/16" High Speed Jobber Drill, 118° Point, Steel
Weight per unit	52.6 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Flute Length	2-5/16"
Material	Steel
Number of Pieces	1
Point Type	Standard
Shank Diameter	3/16"

### Material, Color, and Finish

Finish	Two Tone
--------	----------

### Dimensions and Weight

Overall Length	3-1/2" in
Size	3/16" in

### Descriptions

Description	3/16" HIGH SPEED JOBBER DRILL, 118 POINT, STEEL
extra long description	CUL 91609 3/16 HSS JOBBER DRILL
Features	Jobber Length, 118 Degree Point, General Purpose Drill Bit, Ground Flute, Straight Shank, Bright Finish, M2 High Speed Steel
Long Description	3/16" High Speed Jobber Drill, 118° Point, Steel
Product Type	3/16 HSS Jobber Drill
Special Features	Features a polished flute for easy chip removal.

### Manufacturer Information

Brand	CULLY
GTIN	00085937916099
Manufacturers Part Number	91609
UPC	085937916099

### Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	High Speed Steel Jobber Drill Bit

### Packaging

Carton	12
Weight Per each	52.632



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Jobber Drill Bits are manufactured in a number of different styles for purpose in a variety of different applications making them among the most popular drill bits. Considered an all purpose drill bit Jobbers are most notable for having a long length compared to its diameter.

---