



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

91609 3/16" High Speed Jobber Drill, 118 Point, Steel

Minerallac Company

Catalog Number	91609
Manufacturer	Minerallac Company
Description	3/16" High Speed Jobber Drill, 118° Point, Steel
Weight per unit	52.6 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Flute Length	2-5/16"
Material	Steel
Number of Pieces	1
Point Type	Standard
Shank Diameter	3/16"

Material, Color, and Finish

Finish	Two Tone
--------	----------

Dimensions and Weight

Overall Length	3-1/2" in
Size	3/16" in

Descriptions

Description	3/16" HIGH SPEED JOBBER DRILL, 118 POINT, STEEL
extra long description	CUL 91609 3/16 HSS JOBBER DRILL
Features	Jobber Length, 118 Degree Point, General Purpose Drill Bit, Ground Flute, Straight Shank, Bright Finish, M2 High Speed Steel
Long Description	3/16" High Speed Jobber Drill, 118° Point, Steel
Product Type	3/16 HSS Jobber Drill
Special Features	Features a polished flute for easy chip removal.

Manufacturer Information

Brand	CULLY
GTIN	00085937916099
Manufacturers Part Number	91609
UPC	085937916099

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	High Speed Steel Jobber Drill Bit

Packaging

Carton	12
Weight Per each	52.632



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Jobber Drill Bits are manufactured in a number of different styles for purpose in a variety of different applications making them among the most popular drill bits. Considered an all purpose drill bit Jobbers are most notable for having a long length compared to its diameter.
