



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 92705 Insite RTQ RG-6 BNC Comp Connector 4/Card

*Ideal*

Catalog Number	92705
Manufacturer	Ideal
Description	Ideal, Compression Connector, BNC, Conductor Range: 029 - 042 In, 20 - 18 Awg Solid Center Conductor, Material: Brass, Finish: Nickel Plated, Nominal Impedance: 75 Ohm, Dielectric Diameter: 0.175 - 0.183 In, Coaxial Cable Type: RG-6, Overall Jacket Diameter: 0.260 - 0.305 In
Weight per unit	0.0500 (lbs/each)
Product Category	Coaxial & Twinaxial Connectors

### Features

Material	Brass
----------	-------

### Material, Color, and Finish

Finish	Nickel Plated
--------	---------------

### Descriptions

Description	INSITE RTQ RG-6 BNC COMP CONNECTOR 4/CARD
extra long description	IDEAL 92-705 RG-6 BNC COMPRESSION C
Features	Connector Model: 6BNCISRTQAccepts RG-6/RG-6 Quad/RG-6 Plenum/RG-6 Plenum Quad coax cablesCenter conductor range: 23-18 AWG Solid (.023" - .040")Dielectric diameter range: .168" - .183"Outer jacket diameter range: .226" - .305"Connector Model: 6BNCISRTQAccepts RG-6/RG-6 Quad/RG-6 Plenum/RG-6 Plenum Quad coax cablesCenter conductor range: 23-18 AWG Solid (.023" - .040")Dielectric diameter range: .168" - .183"Outer jacket diameter range: .226" - .305"Recommended cable prep/stripping tools: 45-605 PrepPRORecom
Long Description	IDEAL, Compression Connector, BNC, Conductor Range: 029 - 042 IN, 20 - 18 AWG Solid Center Conductor, Material: Brass, Finish: Nickel Plated, Nominal Impedance: 75 OHM, Dielectric Diameter: 0.175 - 0.183 IN, Coaxial Cable Type: RG-6, Overall Jacket Diameter: 0.260 - 0.305 IN
Product Type	RG-6 BNC Compression Conn 4-PK
Special Features	Features: Nickel-Plated, Brass-Construction For Superior Corrosion Resistance; Moisture-Inhibiting Design; Approved For Indoor And Outdoor Use; Use 30-793 Compression Tool; 75 OHM Nominal Impedance; Gold-Plated Pin Contact Area; Available In Plenum Versions; Nominal Impedance: 75 OHM; Dielectric Diameter: 0.175 - 0.183 IN; Coaxial Cable Type: RG-6; Overall Jacket Diameter: 0.260 - 0.305 IN



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Ideal
GTIN	00783250927050
Manufacturers Part Number	92-705
UPC	783250927050

## Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	BNC

## Packaging

Carton	4
Package	20
Weight Per each	0.05

## Uses, Certifications, and Standards

Application	For CCTV System Installations/Integrations And General Purpose Applications on RG 6 Cable
-------------	---