ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



# 92705 Insite RTQ RG-6 BNC Compression Connector, 4/Card

*Ideal*

| | |
|---|---|
| Catalog Number | 92705 |
| Manufacturer | Ideal |
| Description | Ideal, Compression Connector, BNC, Conductor Range: 029 - 042 In, 20 - 18 Awg Solid Center Conductor, Material: Brass, Finish: Nickel Plated, Nominal Impedance: 75 Ohm, Dielectric Diameter: 0.175 - 0.183 In, Coaxial Cable Type: RG-6, Overall Jacket Diameter: 0.260 - 0.305 In |
| Weight per unit | 0.2000 (lbs/each) |
| Product Category | Coaxial & Twinaxial Connectors |

## Features

| | |
|---|---|
| Material | Brass |

## Material, Color, and Finish

| | |
|---|---|
| Finish | Nickel Plated |

## Descriptions

| | |
|---|---|
| Description | INSITE RTQ RG-6 BNC COMPRESSION CONNECTOR, 4/CARD |
| extra long description | IDEAL 92-705 RG-6 BNC COMPRESSION C |
| Features | Connector Model: 6BNCISRTQAccepts RG-6/RG-6 Quad/RG-6 Plenum/RG-6 Plenum Quad coax cablesCenter conductor range: 23-18 AWG Solid (.023” - .040”)Dielectric diameter range: .168” - .183”Outer jacket diameter range: .226” - .305”Connector Model: 6BNCISRTQAccepts RG-6/RG-6 Quad/RG-6 Plenum/RG-6 Plenum Quad coax cablesCenter conductor range: 23-18 AWG Solid (.023” - .040”)Dielectric diameter range: .168” - .183”Outer jacket diameter range: .226” - .305”Recommended cable prep/stripping tools: 45-605 PrepPRORecom |
| Long Description | IDEAL, Compression Connector, BNC, Conductor Range: 029 - 042 IN, 20 - 18 AWG Solid Center Conductor, Material: Brass, Finish: Nickel Plated, Nominal Impedance: 75 OHM, Dielectric Diameter: 0.175 - 0.183 IN, Coaxial Cable Type: RG-6, Overall Jacket Diameter: 0.260 - 0.305 IN |
| Product Type | RG-6 BNC Compression Conn 4-PK |
| Special Features | Features: Nickel-Plated, Brass-Construction For Superior Corrosion Resistance; Moisture-Inhibiting Design; Approved For Indoor And Outdoor Use; Use 30-793 Compression Tool; 75 OHM Nominal Impedance; Gold-Plated Pin Contact Area; Available In Plenum Versions; Nominal Impedance: 75 OHM; Dielectric Diameter: 0.175 - 0.183 IN; Coaxial Cable Type: RG-6; Overall Jacket Diameter: 0.260 - 0.305 IN |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Manufacturer Information

| | |
|---|---|
| Brand | Ideal |
| GTIN | 00783250927050 |
| Manufacturers Part Number | 92-705 |
| UPC | 783250927050 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Datacom Wiring Devices and Accessories |
| Type | BNC |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Package | 20 |
| Weight Per each | 0.2 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | For CCTV System Installations/Integrations And General Purpose Applications on RG 6 Cable |