

fiberglass BOX™ 3-1/2" Dia. Round Outlet

For Old Work/Manufactured Housing Applications



9305-SC2



9305-SK



9305-SG



9305-SGK



9355-SK

NOTE: All 3-1/2" round outlet boxes have a fixture mounting pattern (at a width of 2.75") with machine tapped holes to accept #8-32 mounting hardware.

Snap Brackets – Wall Applications

Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
			D	W				
14.0	9305-S	3/0 box with flange, snap bracket, Speed Klamps™ - bulk packed	1-3/4	3-1/2	15 lb.	27350	50	21
14.0	9305-SC2	3/0 box with flange, snap bracket, 2 wire clamps - factory installed	1-3/4	3-1/2	15 lb.	27360	50	23
14.0	9305-SK	3/0 box with flange, snap bracket, Speed Klamps™ - factory installed	1-3/4	3-1/2	15 lb.	27351	50	22
14.0	9305-SG	3/0 box with flange, snap bracket, ground strap, Speed Klamps™ - bulk packed	1-3/4	3-1/2	15 lb.	27370	50	23
14.0	9305-SGK	3/0 box with flange, snap bracket, ground strap, Speed Klamps™ - factory installed	1-3/4	3-1/2	15 lb.	27371	50	23
22.0	9355-S	3/0 box with flange, snap bracket, Speed Klamps™ - bulk packed	2-3/4	3-1/2	15 lb.	10480	48	27
22.0	9355-SK	3/0 box with flange, snap bracket, 2 wire clamps - factory installed	2-3/4	3-1/2	15 lb.	68292	48	27
22.0	9355-SGK	3/0 box with flange, snap bracket, ground strap, 2 wire clamps - factory installed	2-3/4	3-1/2	15 lb.	68151	48	26



9304*



9304-G*



9305-C2



9305-K



9305-GK



9355-K



9355-GK

Bottom Mount – Ceiling Fixture Applications

Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
			D	W				
3.5	9304	Fixture mounting holes on 2-3/4" centers, not UL® listed. See NEC 2008 410.10. *For wall applications only.	5/8	3-3/8	—	10025	100	12
3.5	9304-G	Fixture mounting holes on 2-3/4" centers, ground strap, not UL® listed. See NEC 2008 410.10. *For wall applications only.	5/8	3-3/8	—	10026	100	14
14.0	9305	3/0 box with flange, Speed Klamps™ - bulk packed	1-3/4	3-1/2	50 lb. ◀	10030	50	15
14.0	9305-C2	3/0 box with flange, 2 wire clamps - factory installed	1-3/4	3-1/2	50 lb. ◀	10032	50	17
14.0	9305-K	3/0 box with flange, Speed Klamps™ - factory installed	1-3/4	3-1/2	50 lb. ◀	10034	50	16
14.0	9305-G	3/0 box with flange, ground strap, Speed Klamps™ - bulk packed	1-3/4	3-1/2	50 lb. ◀	10031	50	16
14.0	9305-GK	3/0 box with flange, ground strap, Speed Klamps™ - factory installed	1-3/4	3-1/2	50 lb. ◀	10036	50	17
22.0	9355	3/0 box with flange, Speed Klamps™ - bulk packed	2-3/4	3-1/2	50 lb. ◀	10490	48	19
22.0	9355-K	3/0 box with flange, ground strap, Speed Klamps™ - factory installed	2-3/4	3-1/2	50 lb. ◀	68291	48	19
22.0	9355-G	3/0 box with flange, ground strap, Speed Klamps™ - bulk packed	2-3/4	3-1/2	50 lb. ◀	10491	48	19
22.0	9355-GK	3/0 box with flange, ground strap, Speed Klamps™ - factory installed	2-3/4	3-1/2	50 lb. ◀	68091	48	20

All dimensions are in inches unless otherwise noted.
See page 7 for Attachment Coding suffix descriptions.

◀ 50 lb. ceiling fixture rating when bottom mounted per installation instructions.

Old Work/Manufactured Housing Boxes



UL LISTED
Outlet Box

UL File No. E30594

Competitive Cross Reference

Fiberglass Outlet Boxes



ALLIED
MOULDED
PRODUCTS, Inc.

fiberglassBOX™: Premium Series “Hard Box” Fiberglass Boxes continued

Allied Moulded	Carlton® PH (Union Phenolic)	Carlton® PC Black Polycarbonate	Carlton® PVC (Zip Blue)	Carlton® PVC (SuperBlue®)	Cantex® (EZ BOX®)	Pass & Seymour (Slater®)
3300-Z4K	N/A	N/A	N/A	N/A	N/A	N/A
3303-2Z4	N/A	N/A	N/A	N/A	N/A	N/A
3303-2Z4K	N/A	N/A	N/A	N/A	N/A	N/A
3303-N	1063/C	N/A	N/A	BH353A	N/A	S354RAC
3303-NB	N/A	N/A	N/A	N/A	N/A	N/A
3303-NBK	N/A	N/A	N/A	N/A	N/A	N/A
3303-NK	1063/C	N/A	N/A	BH353A	EZ74TN	S354RAC
3303-SS	1063-CS	N/A	N/A	BH353S	N/A	S354RACS
3303-SSK	1063-CS	N/A	N/A	BH353S	EZ74TNZ	S354RACS
3303-Z4	N/A	N/A	SB357	N/A	N/A	S354S50AC
3303-Z4K	N/A	N/A	SB357	N/A	N/A	S354S50AC
4300-2Z2	2004-238/2004-238-02	460-LB	N/A	N/A	N/A	S468S50AC
4300-2Z2K	2004-238/2004-238-02	460-LB	N/A	N/A	N/A	N/A
4300-N	2004	N/A	B455A	BH464A	EZ55QNB	S468RAC
4300-NB	7074BH/2004BH	460-SB	B455AH	N/A	EZ55QNB	N/A
4300-NBK	7074BH/2004BH	460-SB	B455AH	N/A	EZ55QNB	N/A
4300-NK	2004	N/A	B455A	BH464A	EZ55QNB	S468RAC
4300-SS	N/A	N/A	N/A	BH464S	EZ55QNBZ	S468RACS
4300-SSB	N/A	N/A	N/A	N/A	EZ55QNBZ	N/A
4300-SSBK	N/A	N/A	N/A	N/A	EZ55QNBZ	N/A
4300-SSK	N/A	N/A	N/A	BH464S	EZ55QNBZ	S468RACS
4300-Z2	N/A	N/A	N/A	N/A	N/A	N/A
4300-Z2B	N/A	N/A	N/A	N/A	N/A	N/A
4300-Z2BK	N/A	N/A	N/A	N/A	N/A	N/A
4300-Z2K	N/A	N/A	N/A	N/A	N/A	N/A
4300-Z4	N/A	N/A	N/A	N/A	N/A	N/A
4300-Z4K	N/A	N/A	N/A	N/A	N/A	N/A
4304-2Z4	N/A	N/A	N/A	N/A	N/A	N/A
4304-2Z4K	N/A	N/A	N/A	N/A	N/A	N/A
4304-N	N/A	N/A	N/A	BH464A	N/A	N/A
4304-NB	N/A	N/A	N/A	N/A	N/A	N/A
4304-NBK	N/A	N/A	N/A	N/A	N/A	N/A
4304-NK	N/A	N/A	N/A	BH464A	N/A	N/A
4304-Z4B	N/A	N/A	N/A	N/A	N/A	N/A
4304-Z4BK	N/A	N/A	N/A	N/A	N/A	N/A
5305-NBK	N/A	N/A	N/A	N/A	N/A	N/A
5305-NK	N/A	N/A	N/A	N/A	N/A	N/A
5305-Z4BK	N/A	N/A	N/A	N/A	N/A	N/A
9301-E	7060	108E	B108R	N/A	EZ08SF	N/A
9303-H	9050-702	N/A	B108B	N/A	EZ08SB	N/A
9304	3060	N/A	N/A	N/A	N/A	N/A
9304-G	N/A	N/A	N/A	N/A	N/A	N/A
9305	3030	N/A	N/A	N/A	N/A	N/A
9305-G	N/A	N/A	N/A	N/A	N/A	N/A
9305-GK	3030-02-40	N/A	N/A	N/A	N/A	N/A
9305-K	3030PC	N/A	N/A	N/A	N/A	N/A
9305-S	3030-902/3080-9	N/A	N/A	BH614R	N/A	N/A
9305-SG	3020-9-40/3020-902-40	N/A	N/A	BH614P	N/A	N/A
9305-SGK	3020-9-40/3020-902-40	N/A	N/A	BH614P	N/A	N/A
9305-SK	3030-902/3080-9	N/A	N/A	BH614R	N/A	N/A



9305-SC2



9305-SK



9305-SG



9305-SGK



9355-SK

NOTE: All 3-1/2" round outlet boxes have a fixture mounting pattern (at a width of 2.75") with machine tapped holes to accept #8-32 mounting hardware.

Snap Brackets – Wall Applications	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W				
	14.0	9305-S	3/0 box with flange, snap bracket, Speed Klamps™ - bulk packed	1-3/4	3-1/2	15 lb.	27350	50	21
	14.0	9305-SC2	3/0 box with flange, snap bracket, 2 wire clamps - factory installed	1-3/4	3-1/2	15 lb.	27360	50	23
	14.0	9305-SK	3/0 box with flange, snap bracket, Speed Klamps™ - factory installed	1-3/4	3-1/2	15 lb.	27351	50	22
	14.0	9305-SG	3/0 box with flange, snap bracket, ground strap, Speed Klamps™ - bulk packed	1-3/4	3-1/2	15 lb.	27370	50	23
	14.0	9305-SGK	3/0 box with flange, snap bracket, ground strap, Speed Klamps™ - factory installed	1-3/4	3-1/2	15 lb.	27371	50	23
	22.0	9355-S	3/0 box with flange, snap bracket, Speed Klamps™ - bulk packed	2-3/4	3-1/2	15 lb.	10480	48	27
	22.0	9355-SK	3/0 box with flange, snap bracket, 2 wire clamps - factory installed	2-3/4	3-1/2	15 lb.	68292	48	27
	22.0	9355-SGK	3/0 box with flange, snap bracket, ground strap, 2 wire clamps - factory installed	2-3/4	3-1/2	15 lb.	68151	48	26



9304*



9304-G*



9305-C2



9305-K



9305-GK



9355-K



9355-GK

Bottom Mount – Ceiling Fixture Applications	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W				
	3.5	9304	Fixture mounting holes on 2-3/4" centers, not UL® listed. See NEC 2008 410.10. *For wall applications only.	5/8	3-3/8	—	10025	100	12
	3.5	9304-G	Fixture mounting holes on 2-3/4" centers, ground strap, not UL® listed. See NEC 2008 410.10. *For wall applications only.	5/8	3-3/8	—	10026	100	14
	14.0	9305	3/0 box with flange, Speed Klamps™ - bulk packed	1-3/4	3-1/2	50 lb. ◀	10030	50	15
	14.0	9305-C2	3/0 box with flange, 2 wire clamps - factory installed	1-3/4	3-1/2	50 lb. ◀	10032	50	17
	14.0	9305-K	3/0 box with flange, Speed Klamps™ - factory installed	1-3/4	3-1/2	50 lb. ◀	10034	50	16
	14.0	9305-G	3/0 box with flange, ground strap, Speed Klamps™ - bulk packed	1-3/4	3-1/2	50 lb. ◀	10031	50	16
	14.0	9305-GK	3/0 box with flange, ground strap, Speed Klamps™ - factory installed	1-3/4	3-1/2	50 lb. ◀	10036	50	17
	22.0	9355	3/0 box with flange, Speed Klamps™ - bulk packed	2-3/4	3-1/2	50 lb. ◀	10490	48	19
	22.0	9355-K	3/0 box with flange, ground strap, Speed Klamps™ - factory installed	2-3/4	3-1/2	50 lb. ◀	68291	48	19
	22.0	9355-G	3/0 box with flange, ground strap, Speed Klamps™ - bulk packed	2-3/4	3-1/2	50 lb. ◀	10491	48	19
	22.0	9355-GK	3/0 box with flange, ground strap, Speed Klamps™ - factory installed	2-3/4	3-1/2	50 lb. ◀	68091	48	20

All dimensions are in inches unless otherwise noted.
See page 7 for Attachment Coding suffix descriptions.

◀ 50 lb. ceiling fixture rating when bottom mounted per installation instructions.



Old Work/Manufactured Housing Boxes



Outlet Box

UL File No. E30594

Competitive Cross Reference

Fiberglass Outlet Boxes



ALLIED
MOULDED
PRODUCTS, Inc.

fiberglassBOX™: Premium Series “Hard Box” Fiberglass Boxes continued

Allied Moulded	Carlton® PH (Union Phenolic)	Carlton® PC Black Polycarbonate	Carlton® PVC (Zip Blue)	Carlton® PVC (SuperBlue®)	Cantex® (EZ BOX®)	Pass & Seymour (Slater®)
3300-Z4K	N/A	N/A	N/A	N/A	N/A	N/A
3303-2Z4	N/A	N/A	N/A	N/A	N/A	N/A
3303-2Z4K	N/A	N/A	N/A	N/A	N/A	N/A
3303-N	1063/C	N/A	N/A	BH353A	N/A	S354RAC
3303-NB	N/A	N/A	N/A	N/A	N/A	N/A
3303-NBK	N/A	N/A	N/A	N/A	N/A	N/A
3303-NK	1063/C	N/A	N/A	BH353A	EZ74TN	S354RAC
3303-SS	1063-CS	N/A	N/A	BH353S	N/A	S354RACS
3303-SSK	1063-CS	N/A	N/A	BH353S	EZ74TNZ	S354RACS
3303-Z4	N/A	N/A	SB357	N/A	N/A	S354S50AC
3303-Z4K	N/A	N/A	SB357	N/A	N/A	S354S50AC
4300-2Z2	2004-238/2004-238-02	460-LB	N/A	N/A	N/A	S468S50AC
4300-2Z2K	2004-238/2004-238-02	460-LB	N/A	N/A	N/A	N/A
4300-N	2004	N/A	B455A	BH464A	EZ55QNB	S468RAC
4300-NB	7074BH/2004BH	460-SB	B455AH	N/A	EZ55QNB	N/A
4300-NBK	7074BH/2004BH	460-SB	B455AH	N/A	EZ55QNB	N/A
4300-NK	2004	N/A	B455A	BH464A	EZ55QNB	S468RAC
4300-SS	N/A	N/A	N/A	BH464S	EZ55QNBZ	S468RACS
4300-SSB	N/A	N/A	N/A	N/A	EZ55QNBZ	N/A
4300-SSBK	N/A	N/A	N/A	N/A	EZ55QNBZ	N/A
4300-SSK	N/A	N/A	N/A	BH464S	EZ55QNBZ	S468RACS
4300-Z2	N/A	N/A	N/A	N/A	N/A	N/A
4300-Z2B	N/A	N/A	N/A	N/A	N/A	N/A
4300-Z2BK	N/A	N/A	N/A	N/A	N/A	N/A
4300-Z2K	N/A	N/A	N/A	N/A	N/A	N/A
4300-Z4	N/A	N/A	N/A	N/A	N/A	N/A
4300-Z4K	N/A	N/A	N/A	N/A	N/A	N/A
4304-2Z4	N/A	N/A	N/A	N/A	N/A	N/A
4304-2Z4K	N/A	N/A	N/A	N/A	N/A	N/A
4304-N	N/A	N/A	N/A	BH464A	N/A	N/A
4304-NB	N/A	N/A	N/A	N/A	N/A	N/A
4304-NBK	N/A	N/A	N/A	N/A	N/A	N/A
4304-NK	N/A	N/A	N/A	BH464A	N/A	N/A
4304-Z4B	N/A	N/A	N/A	N/A	N/A	N/A
4304-Z4BK	N/A	N/A	N/A	N/A	N/A	N/A
5305-NBK	N/A	N/A	N/A	N/A	N/A	N/A
5305-NK	N/A	N/A	N/A	N/A	N/A	N/A
5305-Z4BK	N/A	N/A	N/A	N/A	N/A	N/A
9301-E	7060	108E	B108R	N/A	EZ08SF	N/A
9303-H	9050-702	N/A	B108B	N/A	EZ08SB	N/A
9304	3060	N/A	N/A	N/A	N/A	N/A
9304-G	N/A	N/A	N/A	N/A	N/A	N/A
9305	3030	N/A	N/A	N/A	N/A	N/A
9305-G	N/A	N/A	N/A	N/A	N/A	N/A
9305-GK	3030-02-40	N/A	N/A	N/A	N/A	N/A
9305-K	3030PC	N/A	N/A	N/A	N/A	N/A
9305-S	3030-902/3080-9	N/A	N/A	BH614R	N/A	N/A
9305-SG	3020-9-40/3020-902-40	N/A	N/A	BH614P	N/A	N/A
9305-SGK	3020-9-40/3020-902-40	N/A	N/A	BH614P	N/A	N/A
9305-SK	3030-902/3080-9	N/A	N/A	BH614R	N/A	N/A