



9331-EWC2











9331-EWK


9363-EWC2

9363-EWK

9366-EWK

9368-EWK

	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
<b>Ears &amp; Wing Brackets</b>	14.0	9331-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	2-½	2-3/8	3-¼	38500	100	30
	14.0	9331-EWC2	 Ears, wing brackets, 2 wire clamps - factory installed	2-½	2-3/8	3-¼	38510	100	33
	14.0	9331-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	2-½	2-3/8	3-¼	38511	100	31
	16.0	9363-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	2-27/32	2-3/8	3-¼	10572	100	32
	16.0	9363-EWC2	 Ears, wing brackets, 2 wire clamps - factory installed	2-27/32	2-3/8	3-¼	10573	100	36
	16.0	9363-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	2-27/32	2-3/8	3-¼	10578	100	33
	18.0	9366-EW	 Wide body box, ears, wing brackets, Speed Klamps™ - bulk packed <i>*Requires oversized device/receptacle plate</i>	2-27/32	2-¾	3-¼	77001	100	34
	18.0	9366-EWK	 Wide body box, ears, wing brackets, Speed Klamps™ - factory installed <i>*Requires oversized device/receptacle plate</i>	2-27/32	2-¾	3-¼	77002	100	35
	18.0	9368-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	3-3/16	2-3/8	3-¼	76002	100	32
	18.0	9368-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	3-3/16	2-3/8	3-¼	76001	100	34



9303-H

9367-E




1TP

9318

9319

9320

9322

	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
<b>Miscellaneous</b>	6.0	9303-H	Side mount hanger, ¼" offset, not UL® listed	1-1/16	2-¼	3-5/8	10021	100	20
	16.0	9367-E	 Side cube box, ears	1-11/16	2-3/8 open 4-15/16 overall	3-¼	75600	50	17
	16.0	9367-EW	 Side cub box, ears, wing brackets	1-11/16	2-3/8 open 4-15/16 overall	3-¼	75601	50	18
	—	1TP	 Metal template for single gang old work box: Series 9331-E, 9363-E, & 9368-E	0.062	4	6	88015	1	1

	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
<b>Handy Box &amp; Covers</b>	12.5	9318	Handy Box surface mounted box with side and bottom cable openings	2	2-¼	4-3/16	10140	100	28
	—	9319	Handy Box switch cover, not UL® listed	—	2-¼	4-¼	10145	100	8
	—	9320	Handy Box duplex outlet cover, not UL® listed	—	2-3/16	4-¼	10146	100	7
	—	9322	Handy Box blank cover, not UL® listed	—	2-3/16	4-3/16	10148	100	7

All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

 Old Work/Manufactured Housing Boxes

 Flush-Device Box  
UL File No. E30594

# Competitive Cross Reference


Fiberglass Outlet Boxes













ALLIED  
MOULDED  
PRODUCTS, Inc.


## fiberglassBOX™: Premium Series “Hard Box” Fiberglass Boxes continued

Allied Moulded	Carlton® PH (Union Phenolic)	Carlton® PC Black Polycarbonate	Carlton® PVC (Zip Blue)	Carlton® PVC (SuperBlue®)	Cantex® (EZ BOX®)	Pass & Seymour (Slater®)
9312-E	N/A	N/A	N/A	N/A	N/A	N/A
9312-EK	N/A	N/A	N/A	N/A	N/A	N/A
9312-EW	6062-402	4R-B	B225R	N/A	EZ25D0	N/A
9312-EWK	6062-402	4R-B	B225R	N/A	EZ25D0	N/A
9313-EW	6063-402	N/A	B355R	N/A	N/A	S3-52-W
9313-EWK	6063-402	N/A	B355R	N/A	N/A	S3-52-W
9314-EWK	N/A	N/A	B468R	N/A	N/A	N/A
9315	4062/WHITE	4R-B	E460R	N/A	EZYKL	N/A
9315-WH	4062/WHITE	4R-B	E460R	N/A	EZYKL	N/A
9318	N/A	N/A	B112HB	N/A	N/A	N/A
9319	N/A	N/A	HB15W	N/A	N/A	N/A
9320	N/A	N/A	HB1DP	N/A	N/A	N/A
9322	N/A	N/A	HB1BL	N/A	N/A	N/A
9324-N	2070/N1614	N/A	N1614	N/A	N/A	N/A
9327-N	6090/7010/E1614	N/A	N/A	N/A	N/A	N/A
9329-EW	7010-8	232-OW	B225R	BH234R	N/A	S2-32-W
9329-EWK	7010-8	232-OW	B225R	BH234R	N/A	S2-32-W
9331-E	6090/7010	N/A	E1614	N/A	N/A	N/A
9331-EK	6090/7010	N/A	E1614	N/A	N/A	N/A
9331-ES	7010-8	N/A	N/A	N/A	N/A	N/A
9331-ESK	7010-8	N/A	N/A	N/A	N/A	N/A
9331-EW	6090-402	114-OW	B114R	N/A	EZ14S0	N/A
9331-EWK	6090-402	114-OW	B114R	N/A	EZ14S0	N/A
9335-16/16K	3190-C-94	N-321-C-94	N/A	N/A	N/A	N/A
9335-16G/16GK	N/A	N-321-GC-94	N/A	N/A	N/A	N/A
9335-BH/BHK	3190-C-94	N-321-C-95	N/A	N/A	N/A	S118HAC
9335-BHG/BHGK	N/A	N-321-GC-95	N/A	N/A	N/A	S118HGAC
9335-HNGK	N/A	N/A	N/A	N/A	N/A	N/A
9335-HNK	N/A	N/A	N/A	N/A	N/A	N/A
9335-N	3190/3190C	N/A	B518A/N-321-C	N/A	EZ18CN	C118RAC
9335-NG	3190-40-PC	N/A	B518P	N/A	EZ18CNG	C118RGAC
9335-NGK	3190-40-PC	N/A	B518P	N/A	EZ18CNG	C118RGAC
9335-NK	3190/3190C	N/A	B518A/N-321-C	N/A	EZ18CN	C118RAC
9335-NKRED	N/A	3R-16-N-RED	N/A	N/A	EZ18CNAR	N/A
9336-16/16K	3090-94/3090-94-SQ	N/A	N/A	N/A	N/A	N/A
9336-16G/16GK	3090-94-40	N/A	N/A	N/A	N/A	N/A
9336-BH/BHK	3090-95/3090-95-SQ	3R-16-BH	N/A	N/A	N/A	N/A
9336-BHG/BHGK	3090-95-40	3R-16-BHGP	N/A	N/A	N/A	N/A
9336-HNGK	3090-N-40	N/A	N/A	N/A	N/A	N/A
9336-HNK	3090-N	N/A	N/A	N/A	N/A	N/A
9336-N	3190	3R16N	N/A	N/A	N/A	N/A
9336-NG	3190-PC	3R16NGP	N/A	N/A	N/A	N/A
9336-NGK	3190-PC	3R16NGP	N/A	N/A	N/A	N/A
9336-NK	3190	3R16N	N/A	N/A	N/A	N/A
9338-E	3080	N/A	N/A	N/A	N/A	N/A
9338-EK	3080	N/A	N/A	N/A	N/A	N/A
9338-EKT	3080	N/A	N/A	N/A	N/A	N/A
9338-ES	3080-9/3080-9-PC	3R160W	N/A	BH614R	N/A	N/A
9338-ESG	3080-9-40	3R160WGP	B432A	BH614RP	N/A	N/A
9338-ESGK	3080-9-40	3R160WGP	B432A	BH614RP	N/A	C118WGAC



9331-EWC2      9331-EWK      9363-EWC2      9363-EWK      9366-EWK      9368-EWK

Ears & Wing Brackets	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	14.0	9331-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	2-½	2-3/8	3-¼	38500	100	30
	14.0	9331-EWC2	 Ears, wing brackets, 2 wire clamps - factory installed	2-½	2-3/8	3-¼	38510	100	33
	14.0	9331-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	2-½	2-3/8	3-¼	38511	100	31
	16.0	9363-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	2-27/32	2-3/8	3-¼	10572	100	32
	16.0	9363-EWC2	 Ears, wing brackets, 2 wire clamps - factory installed	2-27/32	2-3/8	3-¼	10573	100	36
	16.0	9363-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	2-27/32	2-3/8	3-¼	10578	100	33
	18.0	9366-EW	 Wide body box, ears, wing brackets, Speed Klamps™ - bulk packed *Requires oversized device/receptacle plate	2-27/32	2-¾	3-¼	77001	100	34
	18.0	9366-EWK	 Wide body box, ears, wing brackets, Speed Klamps™ - factory installed *Requires oversized device/receptacle plate	2-27/32	2-¾	3-¼	77002	100	35
	18.0	9368-EW	 Ears, wing brackets, Speed Klamps™ - bulk packed	3-3/16	2-3/8	3-¼	76002	100	32
	18.0	9368-EWK	 Ears, wing brackets, Speed Klamps™ - factory installed	3-3/16	2-3/8	3-¼	76001	100	34



9303-H

9367-E




1TP

9318

9319

9320

9322

Miscellaneous	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	6.0	9303-H	Side mount hanger, ¼" offset, not UL® listed	1-1/16	2-¼	3-5/8	10021	100	20
	16.0	9367-E	 Side cube box, ears	1-11/16	2-3/8 open 4-15/16 overall	3-¼	75600	50	17
	16.0	9367-EW	 Side cub box, ears, wing brackets	1-11/16	2-3/8 open 4-15/16 overall	3-¼	75601	50	18
	—	1TP	 Metal template for single gang old work box: Series 9331-E, 9363-E, & 9368-E	0.062	4	6	88015	1	1

Handy Box & Covers	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	12.5	9318	Handy Box surface mounted box with side and bottom cable openings	2	2-¼	4-3/16	10140	100	28
	—	9319	Handy Box switch cover, not UL® listed	—	2-¼	4-¼	10145	100	8
	—	9320	Handy Box duplex outlet cover, not UL® listed	—	2-3/16	4-¼	10146	100	7
	—	9322	Handy Box blank cover, not UL® listed	—	2-3/16	4-3/16	10148	100	7

All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

 Old Work/Manufactured Housing Boxes

 Flush-Device Box  
UL File No. E30594

# Competitive Cross Reference

Fiberglass Outlet Boxes



ALLIED  
MOULDED  
PRODUCTS, Inc.

## fiberglassBOX™: Premium Series “Hard Box” Fiberglass Boxes continued

Allied Moulded	Carlton® PH (Union Phenolic)	Carlton® PC Black Polycarbonate	Carlton® PVC (Zip Blue)	Carlton® PVC (SuperBlue®)	Cantex® (EZ BOX®)	Pass & Seymour (Slater®)
9312-E	N/A	N/A	N/A	N/A	N/A	N/A
9312-EK	N/A	N/A	N/A	N/A	N/A	N/A
9312-EW	6062-402	4R-B	B225R	N/A	EZ25D0	N/A
9312-EWK	6062-402	4R-B	B225R	N/A	EZ25D0	N/A
9313-EW	6063-402	N/A	B355R	N/A	N/A	S3-52-W
9313-EWK	6063-402	N/A	B355R	N/A	N/A	S3-52-W
9314-EWK	N/A	N/A	B468R	N/A	N/A	N/A
9315	4062/WHITE	4R-B	E460R	N/A	EZYKL	N/A
9315-WH	4062/WHITE	4R-B	E460R	N/A	EZYKL	N/A
9318	N/A	N/A	B112HB	N/A	N/A	N/A
9319	N/A	N/A	HB15W	N/A	N/A	N/A
9320	N/A	N/A	HB1DP	N/A	N/A	N/A
9322	N/A	N/A	HB1BL	N/A	N/A	N/A
9324-N	2070/N1614	N/A	N1614	N/A	N/A	N/A
9327-N	6090/7010/E1614	N/A	N/A	N/A	N/A	N/A
9329-EW	7010-8	232-OW	B225R	BH234R	N/A	S2-32-W
9329-EWK	7010-8	232-OW	B225R	BH234R	N/A	S2-32-W
9331-E	6090/7010	N/A	E1614	N/A	N/A	N/A
9331-EK	6090/7010	N/A	E1614	N/A	N/A	N/A
9331-ES	7010-8	N/A	N/A	N/A	N/A	N/A
9331-ESK	7010-8	N/A	N/A	N/A	N/A	N/A
9331-EW	6090-402	114-OW	B114R	N/A	EZ14S0	N/A
9331-EWK	6090-402	114-OW	B114R	N/A	EZ14S0	N/A
9335-16/16K	3190-C-94	N-321-C-94	N/A	N/A	N/A	N/A
9335-16G/16GK	N/A	N-321-GC-94	N/A	N/A	N/A	N/A
9335-BH/BHK	3190-C-94	N-321-C-95	N/A	N/A	N/A	S118HAC
9335-BHG/BHGK	N/A	N-321-GC-95	N/A	N/A	N/A	S118HGAC
9335-HNGK	N/A	N/A	N/A	N/A	N/A	N/A
9335-HNK	N/A	N/A	N/A	N/A	N/A	N/A
9335-N	3190/3190C	N/A	B518A/N-321-C	N/A	EZ18CN	C118RAC
9335-NG	3190-40-PC	N/A	B518P	N/A	EZ18CNG	C118RGAC
9335-NGK	3190-40-PC	N/A	B518P	N/A	EZ18CNG	C118RGAC
9335-NK	3190/3190C	N/A	B518A/N-321-C	N/A	EZ18CN	C118RAC
9335-NKRED	N/A	3R-16-N-RED	N/A	N/A	EZ18CNAR	N/A
9336-16/16K	3090-94/3090-94-SQ	N/A	N/A	N/A	N/A	N/A
9336-16G/16GK	3090-94-40	N/A	N/A	N/A	N/A	N/A
9336-BH/BHK	3090-95/3090-95-SQ	3R-16-BH	N/A	N/A	N/A	N/A
9336-BHG/BHGK	3090-95-40	3R-16-BHGP	N/A	N/A	N/A	N/A
9336-HNGK	3090-N-40	N/A	N/A	N/A	N/A	N/A
9336-HNK	3090-N	N/A	N/A	N/A	N/A	N/A
9336-N	3190	3R16N	N/A	N/A	N/A	N/A
9336-NG	3190-PC	3R16NGP	N/A	N/A	N/A	N/A
9336-NGK	3190-PC	3R16NGP	N/A	N/A	N/A	N/A
9336-NK	3190	3R16N	N/A	N/A	N/A	N/A
9338-E	3080	N/A	N/A	N/A	N/A	N/A
9338-EK	3080	N/A	N/A	N/A	N/A	N/A
9338-EKT	3080	N/A	N/A	N/A	N/A	N/A
9338-ES	3080-9/3080-9-PC	3R160W	N/A	BH614R	N/A	N/A
9338-ESG	3080-9-40	3R160WGP	B432A	BH614RP	N/A	N/A
9338-ESGK	3080-9-40	3R160WGP	B432A	BH614RP	N/A	C118WGAC