


fiberglass BOX™ 3-1/2" Dia. Round Outlet

Wall or Ceiling Fixture Support Boxes



NOTE: All 3-1/2" round outlet boxes have a fixture mounting pattern (at a width of 2.75") with machine tapped holes to accept #8-32 mounting hardware.

Adjustable Bar Hanger for 16" to 24" O.C. Joist Applications	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W				
	16.0	9336-BH	16" - 24" adjustable bar hanger, Speed Klamps™ - bulk packed	2-3/8	3-1/2	50 lb.	88104	24	31
	16.0	9336-BHC2	16" - 24" adjustable bar hanger, 2 wire clamps - factory installed	2-3/8	3-1/2	50 lb.	88118	24	31
	16.0	9336-BHK	16" - 24" adj. bar hanger, Speed Klamps™ - factory installed	2-3/8	3-1/2	50 lb.	88105	24	30
	16.0	9336-BHG	16" - 24" adj. bar hanger, ground strap, Speed Klamps™ - bulk packed	2-3/8	3-1/2	50 lb.	88106	24	30
	16.0	9336-BHGC2	16" - 24" adjustable bar hanger, ground strap, 2 wire clamps - factory installed	2-3/8	3-1/2	50 lb.	88119	24	31
	16.0	9336-BHGK	16" - 24" adjustable bar hanger, ground strap, Speed Klamps™ - factory installed	2-3/8	3-1/2	50 lb.	88107	24	31
	20.5	9335-BH	16" - 24" adjustable bar hanger, Speed Klamps™ - bulk packed	2-15/16	3-1/2	50 lb.	88100	24	32
	20.5	9335-BHC2	16" - 24" adjustable bar hanger, 2 wire clamps - factory installed	2-15/16	3-1/2	50 lb.	88116	24	32
	20.5	9335-BHK	16" - 24" adj. bar hanger, Speed Klamps™ - factory installed	2-15/16	3-1/2	50 lb.	88101	24	32
	20.5	9335-BHG	16" - 24" adjustable bar hanger, ground strap, Speed Klamps™ - bulk packed	2-15/16	3-1/2	50 lb.	88102	24	32
	20.5	9335-BHGC2	16" - 24" adjustable bar hanger, ground strap, 2 wire clamps - factory installed	2-15/16	3-1/2	50 lb.	88117	24	32
	20.5	9335-BHGK	16" - 24" adjustable bar hanger, ground strap, Speed Klamps™ - factory installed	2-15/16	3-1/2	50 lb.	88103	24	32



Bar Hanger for 16" O.C. Joist Applications Only	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W				
	16.0	9336-16	16" bar hanger, Speed Klamps™ - bulk packed	2-3/8	3-1/2	50 lb.	10273	24	20
	16.0	9336-16C2	16" bar hanger, 2 wire clamps - factory installed	2-3/8	3-1/2	50 lb.	98300	24	21
	16.0	9336-16K	16" bar hanger, Speed Klamps™ - factory installed	2-3/8	3-1/2	50 lb.	10284	24	21
	16.0	9336-16G	16" bar hanger, ground strap, Speed Klamps™ - bulk packed	2-3/8	3-1/2	50 lb.	10279	24	20
	16.0	9336-16GC2	16" bar hanger, ground strap, 2 wire clamps - factory installed	2-3/8	3-1/2	50 lb.	10274	24	21
	16.0	9336-16GK	16" bar hanger, ground strap, Speed Klamps™ - factory installed	2-3/8	3-1/2	50 lb.	10286	24	21
	20.5	9335-16	16" bar hanger, Speed Klamps™ - bulk packed	2-15/16	3-1/2	50 lb.	41280	24	21
	20.5	9335-16C2	16" bar hanger, 2 wire clamps - factory installed	2-15/16	3-1/2	50 lb.	41290	24	25
	20.5	9335-16K	16" bar hanger, Speed Klamps™ - factory installed	2-15/16	3-1/2	50 lb.	41281	24	21
	20.5	9335-16G	16" bar hanger, ground strap, Speed Klamps™ - bulk packed	2-15/16	3-1/2	50 lb.	41300	24	21
	20.5	9335-16GC2	16" bar hanger, ground strap, 2 wire clamps - factory installed	2-15/16	3-1/2	50 lb.	41310	24	25
	20.5	9335-16GK	16" bar hanger, ground strap, Speed Klamps™ - factory installed	2-15/16	3-1/2	50 lb.	41301	24	22

All dimensions are in inches unless otherwise noted.
See page 7 for Attachment Coding suffix descriptions.



Competitive Cross Reference

Fiberglass Outlet Boxes



ALLIED
MOULDED
PRODUCTS, Inc.

fiberglassBOX™: Premium Series “Hard Box” Fiberglass Boxes continued

Allied Moulded	Carlton® PH (Union Phenolic)	Carlton® PC Black Polycarbonate	Carlton® PVC (Zip Blue)	Carlton® PVC (SuperBlue®)	Cantex® (EZ BOX®)	Pass & Seymour (Slater®)
9312-E	N/A	N/A	N/A	N/A	N/A	N/A
9312-EK	N/A	N/A	N/A	N/A	N/A	N/A
9312-EW	6062-402	4R-B	B225R	N/A	EZ25D0	N/A
9312-EWK	6062-402	4R-B	B225R	N/A	EZ25D0	N/A
9313-EW	6063-402	N/A	B355R	N/A	N/A	S3-52-W
9313-EWK	6063-402	N/A	B355R	N/A	N/A	S3-52-W
9314-EWK	N/A	N/A	B468R	N/A	N/A	N/A
9315	4062/WHITE	4R-B	E460R	N/A	EZYKL	N/A
9315-WH	4062/WHITE	4R-B	E460R	N/A	EZYKL	N/A
9318	N/A	N/A	B112HB	N/A	N/A	N/A
9319	N/A	N/A	HB15W	N/A	N/A	N/A
9320	N/A	N/A	HB1DP	N/A	N/A	N/A
9322	N/A	N/A	HB1BL	N/A	N/A	N/A
9324-N	2070/N1614	N/A	N1614	N/A	N/A	N/A
9327-N	6090/7010/E1614	N/A	N/A	N/A	N/A	N/A
9329-EW	7010-8	232-OW	B225R	BH234R	N/A	S2-32-W
9329-EWK	7010-8	232-OW	B225R	BH234R	N/A	S2-32-W
9331-E	6090/7010	N/A	E1614	N/A	N/A	N/A
9331-EK	6090/7010	N/A	E1614	N/A	N/A	N/A
9331-ES	7010-8	N/A	N/A	N/A	N/A	N/A
9331-ESK	7010-8	N/A	N/A	N/A	N/A	N/A
9331-EW	6090-402	114-OW	B114R	N/A	EZ14S0	N/A
9331-EWK	6090-402	114-OW	B114R	N/A	EZ14S0	N/A
9335-16/16K	3190-C-94	N-321-C-94	N/A	N/A	N/A	N/A
9335-16G/16GK	N/A	N-321-GC-94	N/A	N/A	N/A	N/A
9335-BH/BHK	3190-C-94	N-321-C-95	N/A	N/A	N/A	S118HAC
9335-BHG/BHGK	N/A	N-321-GC-95	N/A	N/A	N/A	S118HGAC
9335-HNGK	N/A	N/A	N/A	N/A	N/A	N/A
9335-HNK	N/A	N/A	N/A	N/A	N/A	N/A
9335-N	3190/3190C	N/A	B518A/N-321-C	N/A	EZ18CN	C118RAC
9335-NG	3190-40-PC	N/A	B518P	N/A	EZ18CNG	C118RGAC
9335-NGK	3190-40-PC	N/A	B518P	N/A	EZ18CNG	C118RGAC
9335-NK	3190/3190C	N/A	B518A/N-321-C	N/A	EZ18CN	C118RAC
9335-NKRED	N/A	3R-16-N-RED	N/A	N/A	EZ18CNAR	N/A
9336-16/16K	3090-94/3090-94-SQ	N/A	N/A	N/A	N/A	N/A
9336-16G/16GK	3090-94-40	N/A	N/A	N/A	N/A	N/A
9336-BH/BHK	3090-95/3090-95-SQ	3R-16-BH	N/A	N/A	N/A	N/A
9336-BHG/BHGK	3090-95-40	3R-16-BHGP	N/A	N/A	N/A	N/A
9336-HNGK	3090-N-40	N/A	N/A	N/A	N/A	N/A
9336-HNK	3090-N	N/A	N/A	N/A	N/A	N/A
9336-N	3190	3R16N	N/A	N/A	N/A	N/A
9336-NG	3190-PC	3R16NGP	N/A	N/A	N/A	N/A
9336-NGK	3190-PC	3R16NGP	N/A	N/A	N/A	N/A
9336-NK	3190	3R16N	N/A	N/A	N/A	N/A
9338-E	3080	N/A	N/A	N/A	N/A	N/A
9338-EK	3080	N/A	N/A	N/A	N/A	N/A
9338-EKT	3080	N/A	N/A	N/A	N/A	N/A
9338-ES	3080-9/3080-9-PC	3R160W	N/A	BH614R	N/A	N/A
9338-ESG	3080-9-40	3R160WGP	B432A	BH614RP	N/A	N/A
9338-ESGK	3080-9-40	3R160WGP	B432A	BH614RP	N/A	C118WGAC