


# fiberglass BOX™ 3-1/2" Dia. Round Outlet

## Wall or Ceiling Fixture Support Boxes



**NOTE:** All 3-1/2" round outlet boxes have a fixture mounting pattern (at a width of 2.75") with machine tapped holes to accept #8-32 mounting hardware.

Nail-On	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W				
	16.0	9336-N	Fetter ring nails, Speed Klamps™ - bulk packed	2-3/8	3-1/2	50 lb.	10270	50	21
	16.0	9336-NC2	Fetter ring nails, 2 wire clamps - factory installed	2-3/8	3-1/2	50 lb.	10276	50	23
	16.0	9336-NK	Fetter ring nails, Speed Klamps™ - factory installed	2-3/8	3-1/2	50 lb.	10271	50	22
	16.0	9336-NG	Fetter ring nails, ground strap, Speed Klamps™ - bulk packed	2-3/8	3-1/2	50 lb.	10280	50	22
	16.0	9336-NGK	Fetter ring nails, ground strap, Speed Klamps™ - factory installed	2-3/8	3-1/2	50 lb.	10281	50	22
	20.5	9335-N	Fetter ring nails, Speed Klamps™ - bulk packed	2-7/8	3-1/2	50 lb.	41160	50	24
	20.5	9335-NC2	Fetter ring nails, 2 wire clamps - factory installed	2-7/8	3-1/2	50 lb.	41170	50	25
	20.5	9335-NK	Fetter ring nails, Speed Klamps™ - factory installed	2-7/8	3-1/2	50 lb.	41162	50	24
20.5	9335-NKRED	Fetter ring nails, Speed Klamps™ - factory installed *Molded in red for fire circuits	2-7/8	3-1/2	50 lb.	96503	12	6	
20.5	9335-NG	Fetter ring nails, ground strap, Speed Klamps™ - bulk packed	2-7/8	3-1/2	50 lb.	41180	50	25	
20.5	9335-NGC2	Fetter ring nails, ground strap, 2 wire clamps - factory installed	2-7/8	3-1/2	50 lb.	41190	50	26	
20.5	9335-NGK	Fetter ring nails, ground strap, Speed Klamps™ - factory installed	2-7/8	3-1/2	50 lb.	41182	50	25	



"HN" Hanger	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W				
	16.0	9336-HNGK	Nail-on "HN" hanger, ground strap, Speed Klamps™ - factory installed	2-3/8	3-1/2	50 lb.	10341	50	26
	16.0	9336-HNK	Nail-on "HN" hanger, Speed Klamps™ - factory installed	2-3/8	3-1/2	50 lb.	10307	50	25
	20.5	9335-HNGK	Nail-on "HN" hanger, ground strap, Speed Klamps™ - factory installed	2-15/16	3-1/2	50 lb.	41823	50	29
20.5	9335-HNK	Nail-on "HN" hanger, Speed Klamps™ - factory installed	2-15/16	3-1/2	50 lb.	41824	50	28	

All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

