



Powering Business Worldwide

pe.eaton.com

Reversing Drum Switch without Overload Relay

9441H268

UPC:782113202457

Dimensions:

- **Height:** 5.88 IN
- **Length:** 4.38 IN
- **Width:** 2.5 IN

Notes: Field convertible from maintained both positions to momentary both positions

Warranties:

- 1 year

Specifications:

- **Operator:** Lever
- **Mounting:** Surface
- **Number Of Poles:** Three-pole
- **Operation:** Maintained
- **Size:** DB 1

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - 9441H268](#)

Certifications:

- CSA file No. 184-N-13.13A
- UL Listed file E37316
- CSA file No. 229767, Class 3211-05

Product compliance:

- NLRV





Powering Business Worldwide

pe.eaton.com

Reversing Drum Switch without Overload Relay

9441H268

UPC:782113202457

Dimensions:

- **Height:** 5.88 IN
- **Length:** 4.38 IN
- **Width:** 2.5 IN

Notes:Field convertible from maintained both positions to momentary both positions

Warranties:

- 1 year

Specifications:

- **Operator:** Lever
- **Mounting:** Surface
- **Number Of Poles:** Three-pole
- **Operation:** Maintained
- **Size:** DB 1

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - 9441H268](#)

Certifications:

- CSA file No. 184-N-13.13A
- UL Listed file E37316
- CSA file No. 229767, Class 3211-05

Product compliance:

- NLRV

