



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A1086CHQRFGW 10X8X6 N4X FG CH

*Hoffman Enclosures, Inc.*

Catalog Number	A1086CHQRFGW
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge QR Window Cover Enclosure 4X, 10X8X6, Light Gray, Fiberglass
Weight per unit	4.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

### Features

ip rating	IP66
Material	Fiberglass

### Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte

### Dimensions and Weight

Depth	6
Height	10
Size	10.00x8.00x6.00 in
Width	8

### Descriptions

Description	10X8X6 N4X FG CH
extra long description	NVENT HOF A1086CHQRFGW Enclosure 10
Features	The efficient design and simple construction of these enclosures make them durable in corrosive environments, yet aesthetically pleasing. Corner latches provide unobstructed access. The continuous hinge provides a secure seal, and double latching creates added security.
Long Description	Continuous Hinge QR Window Cover Enclosure 4X, 10x8x6, Light Gray, Fiberglass
Product Type	Enclosure 10.00X8.00X6.00

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510312701
Manufacturers Part Number	A1086CHQRFGW
UPC	783510312701

### Taxonomies, Classifications, and Categories

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Window Cover, Quick Release



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	4

## Uses, Certifications, and Standards

Application	Corrosive Environments; Controls and Drives
nema rating	4X Watertight, corrosion-resistant