



A12R126HCR 12X12X6 N3R HC Encl

Hoffman Enclosures, Inc.

Catalog Number	A12R126HCR
Manufacturer	Hoffman Enclosures, Inc.
Description	Enclosure, Steel, Hinge Cover, Panel Mount, Gray, Galvanized Paint, 12 In Overall Width, 12 In Overall Length, 6 In Overall Height, 5 Knockouts, 25.4 LB
Weight per unit	25.4 (lbs/each)
Product Category	Nema Types 3 & 3R Metallic Enc

Material, Color, and Finish

Color Code	ANSI 61
Finish	Powder Coated

Dimensions and Weight

Depth	6
Height	12
Size	12.00x12.00x6.00 in
Width	12

Descriptions

Description	12X12X6 N3R HC ENCL
extra long description	NVENT HOF A12R126HCR Enclosure 12.0
Features	Small Drip-Shield Hinged-Cover, Type 3R protects wiring and other electrical components in outdoor applications that require protection from rain, sleet, snow or dripping water. It offers the flexibility of securing enclosure with an optional padlock in its draw-pull catch and weldnuts for optional panel mounting. These enclosures have a size range of 6 x 4 x 4-in. to 12 x 12 x 10-in.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510387600
UPC	783510387600

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	25.4

Uses, Certifications, and Standards

nema rating	3R
-------------	----