



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A12R126HCR 12X12X6 N3R HC Encl

Hoffman Enclosures, Inc.

| | |
|------------------|--|
| Catalog Number | A12R126HCR |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Enclosure, Steel, Hinge Cover, Panel Mount, Gray, Galvanized Paint, 12 In Overall Width, 12 In Overall Length, 6 In Overall Height, 5 Knockouts, 25.4 LB |
| Weight per unit | 25.4 (lbs/each) |
| Product Category | Nema Types 3 & 3R Metallic Enc |

Material, Color, and Finish

| | |
|------------|---------------|
| Color Code | ANSI 61 |
| Finish | Powder Coated |

Dimensions and Weight

| | |
|--------|---------------------|
| Depth | 6 |
| Height | 12 |
| Size | 12.00x12.00x6.00 in |
| Width | 12 |

Descriptions

| | |
|------------------------|---|
| Description | 12X12X6 N3R HC ENCL |
| extra long description | NVENT HOF A12R126HCR Enclosure 12.0 |
| Features | Small Drip-Shield Hinged-Cover, Type 3R protects wiring and other electrical components in outdoor applications that require protection from rain, sleet, snow or dripping water. It offers the flexibility of securing enclosure with an optional padlock in its draw-pull catch and weldnuts for optional panel mounting. These enclosures have a size range of 6 x 4 x 4-in. to 12 x 12 x 10-in. |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510387600 |
| UPC | 783510387600 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------------------|
| Category Description | STEEL JUNCTION BOXES |
| Type | Wall-Mounted / Pad-Mounted Enclosures |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 25.4 |

Uses, Certifications, and Standards

| | |
|-------------|-----------------------------------|
| nema rating | 3R Weather-resistant, except dust |
|-------------|-----------------------------------|