



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A16148CHQRFQ 16X14X8 N4X FG SLD CH Encl

Hoffman Enclosures, Inc.

Catalog Number	A16148CHQRFQ
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge QR Cover Enclosure 4X, 16X14X8, Light Gray, Fiberglass
Weight per unit	9.9 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

Features

ip rating	IP66
Material	Fiberglass

Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte

Dimensions and Weight

Depth	8
Height	16
Size	16.00x14.00x8.00 in
Width	14

Descriptions

Description	16X14X8 N4X FG SLD CH ENCL
extra long description	NVENT HOF A16148CHQRFQ Enclosure 16
Features	The efficient design and simple construction of these enclosures make them durable in corrosive environments, yet aesthetically pleasing. Corner latches provide unobstructed access. The continuous hinge provides a secure seal, and double latching creates added security.
Long Description	Continuous Hinge QR Cover Enclosure 4X, 16x14x8, Light Gray, Fiberglass
Product Type	Enclosure 16.00X14.00X8.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510298104
Manufacturers Part Number	A16148CHQRFQ
UPC	783510298104

Taxonomies, Classifications, and Categories

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Solid Cover, Quick Release



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	9.92

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X Watertight, corrosion-resistant