



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A161608LP 16X16X8 N12 CLMP CH Encl

Hoffman Enclosures, Inc.

Catalog Number	A161608LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 12, 16X16X8, Gray, Mild Steel
Weight per unit	23.5 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

ip rating	IP65
Material	MILD STEEL

Material, Color, and Finish

Finish	Powder Coated
--------	---------------

Dimensions and Weight

Depth	8
Height	16
Size	16.00x16.00x8.00 in
Width	16

Descriptions

Description	16X16X8 N12 CLMP CH ENCL
extra long description	NVENT HOF A161608LP Enclosure 16.00
Features	For applications requiring a bright white interior to increase control visibility, this enclosure includes a padlocking hasp and staple for security and screw-down clamps for secure closure.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 12, 16x16x8, Gray, Mild Steel
Product Type	Enclosure 16.00X16.00X8.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510278809
Manufacturers Part Number	A161608LP
UPC	783510278809

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	23.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Controls and Drives

nema rating

12 Indoor, dust-resistant