



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A174T100 Area Light 100W 5000K Color Temp

Rab Lighting

Catalog Number	A174T100
Manufacturer	Rab Lighting
Description	Arealights 13927.9 Lumens A17 Type Iv 100W Led 120V-277V Pole Mount Bronze
Weight per unit	11.2 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.80A/0.64A/0.48A @120V 0.46A/0.37A/0.28A @208V 0.42A/0.33A/0.25A @240V 0.36A/0.30A/0.22A @277V
average life	100000
Fixture Type	Suitable for wet locations
lumens	13937.9
Shape	Rectangular
Voltage Rating	120/277
Wattage	100

Material, Color, and Finish

Color	Bronze
-------	--------

Descriptions

Description	AREA LIGHT 100W 5000K COLOR TEMP
extra long description	RAB A17-4T100 Area A17 T4 100W LED
Long Description	Arealights 13927.9 Lumens A17 Type Iv 100W Led 120V-277V Pole Mount Bronze
Product Type	Area A17 T4 100W Led BZ
Special Features	Selectable wattage/CCT

Manufacturer Information

Brand	RAB Lighting Inc
GTIN	00192552002929
Manufacturers Part Number	A17-4T100
UPC	192552002929

Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
Type	AREA LIGHT

Packaging

Carton	1
Weight Per each	11.18

Uses, Certifications, and Standards

Application	Outdoor
Mounting	Universal Pole Mount