



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A1910E26850DIM 10W Led A19 50K 800LM Dim Rab Lighting

Catalog Number	A1910E26850DIM
Manufacturer	Rab Lighting
Description	A Line Bulbs 840 Lumens Led A19 10W 60EQ E26 CRI80 5000K Dimmable
Weight per unit	0.1323 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

average life	15000
Base	E26
beam angle	230
lumens	840
Power Factor	0.7
Shape	A19
Voltage Rating	120
Wattage	10

Material, Color, and Finish

color rendering index (cri)	80 CRI
color temperature	5000

Descriptions

Description	10W LED A19 50K 800LM DIM
extra long description	RAB A19-10-E26-850-DIM LED A19 10W
Long Description	A Line Bulbs 840 Lumens Led A19 10W 60Eq E26 CRI80 5000K Dimmable
Product Type	Led A19 10W 60EQ 840LM E26 5K Dim

Manufacturer Information

Brand	RAB Lighting Inc
GTIN	00019813748221
Manufacturers Part Number	A19-10-E26-850-DIM
UPC	019813748221

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	Lamps

Packaging

Carton	1
Package	12
Weight Per each	0.1323