



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A20H1608GQRLP Hoff A20H1608GQRLP NM4X FBRGLS Enc

*Hoffman Enclosures, Inc.*

Catalog Number	A20H1608GQRLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Hinge Cover Enclosure Quick-Release Type 4X, 20.19X16.25X8.00, Gray, Fiberglass
Weight per unit	19.8 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

### Features

ip rating	IP66
Material	Fiberglass

### Material, Color, and Finish

Color	Gray
Finish	Smooth Matte

### Dimensions and Weight

Depth	8
Height	20.19
Size	20.19x16.25x8.00 in
Width	16.25

### Descriptions

Description	HOFF A20H1608GQRLP NM4X FBRGLS ENC
extra long description	NVENT HOF A20H1608GQRLP Enclosure 2
Features	A full range of modification options are available for wall-mount fiberglass enclosures, including variable depths to accommodate larger controls. These enclosures feature padlockable polyester latches, or HOFFMAN's exclusive PowerGlide Handle with 3-point latching, for ease of access with increased security.
Long Description	Hinge Cover Enclosure Quick-Release Type 4X, 20.19x16.25x8.00, Gray, Fiberglass
Product Type	Enclosure 20.19X16.25X8.00

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510295004
Manufacturers Part Number	A20H1608GQRLP
UPC	783510295004

### Taxonomies, Classifications, and Categories

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	19.8

## Uses, Certifications, and Standards

Application	Corrosive Environments; Controls and Drives
nema rating	4X Watertight, corrosion-resistant