



## A20H16ALP 20X16X6 N4 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A20H16ALP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 20X16X6, Gray, Mild Steel
Weight per unit	25.5 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

### Features

ip rating	IP66
Material	Steel

### Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated

### Dimensions and Weight

Depth	6
Height	20
Size	20.00x16.00x6.00 in
Width	16

### Descriptions

Description	20X16X6 N4 CH CLMP CVR
extra long description	NVENT HOF A20H16ALP Type 4 Encl. 20
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 20x16x6, Gray, Mild Steel
Product Type	Type 4 Encl. 20.00X16.00X6.00

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510243302
Manufacturers Part Number	A20H16ALP
UPC	783510243302

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	25.5

## Uses, Certifications, and Standards

Application	Controls and Drives
nema rating	12