



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A20H2008SSLP 20X20X8 N4X CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A20H2008SSLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 20X20X8, Brushed, SS304
Weight per unit	36.3 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Depth	8
Height	20
Size	20.00x20.00x8.00 in
Width	20

Descriptions

Description	20X20X8 N4X CH CLMP CVR
extra long description	NVENT HOF A20H2008SSLP WALLMOUNT TY
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 20x20x8, Brushed, SS304
Product Type	Wallmount Type 4X Enclosure

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510110888
Manufacturers Part Number	A20H2008SSLP
UPC	783510110888

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	36.2999

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X Watertight, corrosion-resistant