



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A20H2008SSLP 20X20X8 N4X CH CLMP CVR

*Hoffman Enclosures, Inc.*

Catalog Number	A20H2008SSLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 20X20X8, Brushed, SS304
Weight per unit	36.3 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

ip rating	IP66
Material	Stainless Steel 304

### Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

### Dimensions and Weight

Depth	8
Height	20
Size	20.00x20.00x8.00 in
Width	20

### Descriptions

Description	20X20X8 N4X CH CLMP CVR
extra long description	NVENT HOF A20H2008SSLP WALLMOUNT TY
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 20x20x8, Brushed, SS304
Product Type	Wallmount Type 4X Enclosure

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510110888
Manufacturers Part Number	A20H2008SSLP
UPC	783510110888

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	36.2999

## Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X Watertight, corrosion-resistant