



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A242408LP 24X24X8 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

|                  |   |
|------------------|---|
| Catalog Number   | A242408LP   |
| Manufacturer     | Hoffman Enclosures, Inc.  |
| Description      | Wall-Mount Enclosure, Steel, Type 12 Continuous Hinge, Wall Mount, White (Inside);Ansi 61 Gray (Outside), White (Inside);Gray (Door), 24 In Overall Width, 24 In Overall Length, 8 In Overall Height, 43 LB |
| Weight per unit  | 43.0 (lbs/each)   |
| Product Category | Nema Types 12 & 13 Metallic En  |

### Material, Color, and Finish

|        |               |
|--------|---------------|
| Finish | Powder Coated |
|--------|---------------|

### Dimensions and Weight

|        |                     |
|--------|---------------------|
| Depth  | 8                   |
| Height | 24                  |
| Size   | 24.00x24.00x8.00 in |
| Width  | 24                  |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 24X24X8 N12 CH CLMP CVR  |
| extra long description | NVENT HOF A242408LP Enclosure 24.00  |
| Features               | For applications requiring a bright white interior to increase control visibility, this enclosure includes a padlocking hasp and staple for security and screw-down clamps for secure closure. |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Nvent Hoffman  |
| GTIN  | 00783510282103 |
| UPC   | 783510282103   |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | STEEL JUNCTION BOXES                          |
| Type                 | Mild Steel Wall Mounted Industrial Enclosures |

### Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 43 |

### Uses, Certifications, and Standards

|             |                           |
|-------------|---------------------------|
| nema rating | 12 Indoor, dust-resistant |
|-------------|---------------------------|