



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A242410LP 24X24X10 N12 CH CLMP CVR

*Hoffman Enclosures, Inc.*

Catalog Number	A242410LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 12, 24X24X10, Gray, Mild Steel
Weight per unit	53.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

### Features

ip rating	IP65
Material	MILD STEEL

### Material, Color, and Finish

Finish	Powder Coated
--------	---------------

### Dimensions and Weight

Depth	10
Height	24
Size	24.00x24.00x10.00 in
Width	24

### Descriptions

Description	24X24X10 N12 CH CLMP CVR
extra long description	NVENT HOF A242410LP Enclosure 24.00
Features	For applications requiring a bright white interior to increase control visibility, this enclosure includes a padlocking hasp and staple for security and screw-down clamps for secure closure.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 12, 24x24x10, Gray, Mild Steel
Product Type	Enclosure 24.00X24.00X10.00

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510284008
Manufacturers Part Number	A242410LP
UPC	783510284008

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

### Packaging

Carton	1
Weight Per each	53



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....

Controls and Drives .....

nema rating .....

12 Indoor, dust-resistant .....